





CIRCUIT: SPST ▲

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. TERMINAL NUMBERS FOR REF. ONLY
3. TOLERANCE: X.XX=± 0.4
X.XX=± 0.25
4. RATING: 50mA @ 12VDC
5. TRAVEL: 0.25mm +0.2/-0.1mm
- ▲ 6. OPERATING FORCE: 250± 50gf
7. ELECTRICAL LIFE: 100,000 CYCLES MIN.
8. CONTACT RESISTANCE: 100mΩ MAX.
- ▲ 9. CONTACT MATERIAL: GOLD
10. ▲ DENOTES CRITICAL PARAMETER
11. OPERATING TEMP: -40°C TO 85°C



C	24547	CHANGE OPERATING TEMPERATURE	10/6/20	JM	 E-SWITCH®			
B	15513	ADD DOME, ROHS, NOTES EDIT DESC	11/9/05	PH				
A	11176	RELEASED FOR PRODUCTION	1/16/01	CJB	TITLE TL1105SPF250R			
REV	PCR NO	DESCRIPTION	DATE	BY	SCALE	DATE	DR	REV
					4:1	1/16/2001	CJB	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE

4:1

DATE

1/16/2001

DR

CJB

DWG

P010212

REV

C