

ESL 44X7 CUS - Insert strip



0824404

<https://www.phoenixcontact.com/us/products/0824404>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert strip, can be ordered: in sheets, white, labeled according to customer specifications, mounting type: insert, text field height: 7 mm, text field width: 44 mm



Your advantages

- Marker strips for KLM-A terminal strip marker carriers
- Thanks to their special shape, the EMT (44x7)R insert labels remain securely inside the carrier once inserted

Commercial data

Item number	0824404
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8114
Catalog page	Page 501 (C-5-2013)
GTIN	4046356352758
Weight per piece (including packing)	13.48 g
Weight per piece (excluding packing)	13.1 g
Customs tariff number	49119900
Country of origin	DE

ESL 44X7 CUS - Insert strip



0824404

<https://www.phoenixcontact.com/us/products/0824404>

Technical data

Product properties

Product type	Labeled terminal marker
--------------	-------------------------

Marking

Identification technology	Plotter
---------------------------	---------

Mounting

Mounting type	insert
---------------	--------

Material specifications

Foil strength	135 µm
Color	white (RAL 9010)
Material	Polyester foil
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2011 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

ESL 44X7 CUS - Insert strip



0824404

<https://www.phoenixcontact.com/us/products/0824404>

Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Dimensions

Width	44 mm
Length	7 mm

Text field

Text field width	44 mm
Text field height	7 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Notes

General	Print image may vary depending on laser printer
---------	---

ESL 44X7 CUS - Insert strip


0824404

<https://www.phoenixcontact.com/us/products/0824404>



Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

ESL 44X7 CUS - Insert strip

0824404

<https://www.phoenixcontact.com/us/products/0824404>



Classifications

ECLASS

ECLASS-11.0	27281106
ECLASS-12.0	27281106
ECLASS-13.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

ESL 44X7 CUS - Insert strip



0824404

<https://www.phoenixcontact.com/us/products/0824404>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com