


ZBF 3,5:UNBEDRUCKT - Zack Marker strip, flat



0829392

<https://www.phoenixcontact.com/us/products/0829392>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 3.5 mm, Number of individual labels: 10, text field height: 5.2 mm, text field width: 3.5 mm

Your advantages

- Unlabeled marking strips can be custom-labeled with a plotter or by hand
- Other pitches available on request
- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- The multi-section marking strips are easy to fit and can be easily separated if required

Commercial data

Item number	0829392
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2112
Catalog page	Page 126 (C-3-2019)
GTIN	4046356547482
Weight per piece (including packing)	0.468 g
Weight per piece (excluding packing)	0.45 g
Customs tariff number	39269097
Country of origin	DE

ZBF 3,5:UNBEDRUCKT - Zack Marker strip, flat



0829392

<https://www.phoenixcontact.com/us/products/0829392>

Technical data

Product properties

Product type	Terminal marking
Pitch	3.5 mm
Type	flat

Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10

Dimensions

Width	3.5 mm
Pitch	3.5 mm

Text field

Text field width	3.5 mm
Text field height	5.2 mm

Material specifications

Color	white (RAL 9010)
Material	PA
	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
	DIN EN 61010-1 (VDE 0411-1)

Mounting

ZBF 3,5:UNBEDRUCKT - Zack Marker strip, flat



0829392

<https://www.phoenixcontact.com/us/products/0829392>

Mounting type	latching
---------------	----------

Drawings

Schematic diagram



ZBF 3,5:UNBEDRUCKT - Zack Marker strip, flat



0829392

<https://www.phoenixcontact.com/us/products/0829392>

Classifications

ECLASS

ECLASS-13.0	27281101
-------------	----------

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZBF 3,5:UNBEDRUCKT - Zack Marker strip, flat



0829392

<https://www.phoenixcontact.com/us/products/0829392>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.003 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com