


SCHEMATIC



SPECIFICATIONS

FUNCTION:
2P2T ON-ON

RATINGS:
ANSI/UL 1054 and CN/CSA C22.2 No. 55 (E194579):
20A 125VAC 2HP 60Hz [cURus]
20A 250VAC 2HP 60Hz [cURus]

CONTACT RESISTANCE:
Initial: 50mΩ Max.

INSULATION RESISTANCE:
500MΩ Min. at 500VDC

DIELECTRIC STRENGTH:
1,500VAC For 1 Minute

TEMPERATURE:
Operating: -20°C to 85°C [cURus]

INGRESS PROTECTION:
IP55

APPROVALS:



COLORS AND MARKINGS

BODY:
Black

ACTUATOR:
Black

MOUNTING EARS:
White

MARKINGS:
I/O Vertical (1)

MARKING COLOR:
White

MATERIALS

BODY:
Polyamide 6/6 (PA66), UL94 V-0




ACTUATOR:
Polyamide 6/6 (PA66), UL94 V-2

MOUNTING EARS:
Polyamide 6/6 (PA66), UL94 V-2


CONTACTS:
Silver Alloy

TERMINALS:
Silver Plated Copper

RUBBER SEAL:
Ethylene Propylene Thermoplastic Rubber (EPTR)



SUGGESTED PANEL CUTOUT



ACTUATOR	A	08/07/21	CAB
BODY	A	08/07/21	CAB
COLORS	A	08/07/21	CAB
MATERIALS	B	10/12/10	CAB
SPECIFICATIONS	A	08/07/21	CAB
REFERENCE	REV.	DATE	

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

B	CORRECTED TERMINAL PLATING TO SILVER	19461	10/12/10	CAB
A	INITIAL RELEASE	PCRD0038	08/07/21	CAB
REV.	DESCRIPTION	PCR	DATE	DRAWN BY

DIMENSIONS	INCHES [MILLIMETERS]
GENERAL TOLERANCES	±0.008 [±0.2] / ±1°
SCALE	DRAWING NOT TO SCALE



E-SWITCH®



WB24GD1121

ITEM NUMBER	DATE	REVISION
34-WB24GD1121	DECEMBER 10, 2010	B