

SPECIFICATIONS:

ELECTRICAL:

INSULATION RESISTANCE: 1,000 MOhms MIN. **OPERATING TEMPERATURE:** -50°C TO +100°C VOI TAGE: 500 VAC FOR 1 MINUTE

MATERIALS:

INSULATOR: PBT +30% GF. UL94 V-0

PROCESS TEMP: 230°C

SHELL: NICKEL PLATED STEEL

COMPATIBLE WITH NORCOMP CONTACT PART NUMBERS BELOW:


180-002-170L001

180-102-170L001

180-202-170L002

NOTE: CONTACTS MUST BE PURCHASED SEPARATELY

NORCOMP MACHINED CONTACT PART NUMBERS 180-201-170L002 & 180-202-170L002, ONCE INSERTED INTO NORCOMP 180 SERIES CRIMP AND POKE CONNECTORS, CANNOT BE REMOVED.



THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. P. JENKINS

07/19/2005

DATE:

NorComp


DO NOT SCALE FROM DRAWING SCALE: SHEET OF **REV** NTS 24 1

> DWG NO. 180-YYY-27YLYY0


TOLERANCE:

ALL DIMENSIONS ARE ±0.010


ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS



01 0.157" (SOLDER SIDE)



02 0.250" (SOLDER SIDE)



03 0.250" (MATING SIDE)

Roks Compliant

DRAWN: P. JENKINS

DATE: 07/19/2005 UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp DWG NO.

SCALE: SHEET NTS

2

2

REV

24

180-YYY-27YLYY0