


SPECIFICATIONS:

ELECTRICAL:

INSULATOR RESISTANCE: 1000 MOHMS MIN.
SIGNAL CONTACT RESISTANCE: 45 mOHMS MAX.
CONTACT CURRENT RATING: 1 AMP
D.W.V.: 500VAC
OPERATING TEMPERATURE: -55°C TO 85°C

MATERIALS:

INSULATOR: PBT UL94V-0, BLK
230°C MAX PROCESS TEMP
SHELL: ZINC ALLOY
CONTACTS: 15u" GOLD PLATED BERYLLIUM COPPER MATING AREA
TIN PLATED ON SOLDER AREA



DIMENSIONS(mm) ±0.15					
SIZE	A	B	C	D	E
9	19.55	14.35	5.08	3.81	8.20
15	23.36	18.20	8.89	7.62	12.00
25	29.70	24.55	15.24	13.97	18.35

380-YYY-11YL001

SERIES
POSITIONS
009
015
025

PCB CONTACT LENGTH
3 = 2.50mm

NOTE:

**NOT DESIGNED TO MATE WITH NORCOMP 580-M // 581-M SERIES CONNECTORS.
IF ANY QUESTIONS PLEASE CONTACT ENG@NORCOMP.NET

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
08/18/2011

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS


SHEET OF
1 2

REV
8


DWG NO.

380-YYY-113L001


9 POSITION



15 POSITION



25 POSITION



*TYPICAL
PLEASE TEST WITHIN
YOUR SOLDERING
OPERATION TO ENSRUE
THIS IS SUITABLE

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON

DATE: 08/18/2011

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS

SHEET 2 OF 2

REV 8

DWG NO. 380-YYY-113L001