


DESCRIPTION: POWER - RIGHT ANGLE - MALE - MACHINED - IP67



SEE SHEET 2 FOR CONTACT & BRACKET DIMENSION DETAILS SPECIFICATIONS:

ELECTRICAL:

INSULATOR RESISTANCE:

5 GΩ MIN. **DIELECTRIC WITHSTAND VOLTAGE:** 1000 VAC FOR 1 MINUTE

WORKING VOLTAGE:

250V

OPERATING TEMPERATURE: -55°C TO +125°C POWER CONTACT RESISTANCE: $2.0 \text{ m}\Omega$ MAX. POWER CONTACT AMPERAGE: SEE P/N KEY

MECHANICAL:

CONTACT INSERTION FORCE: 4.5 Kg MAX. 0.3 Kg MIN. CONTACT SEPARATION FORCE:

MATERIALS:

CONTACTS: COPPER ALLOY, GOLD FLASH

INSULATOR:

PBT UL94V-0 RATED 230°C PROCESS TEMP.

SHELL: BRACKET: NICKEL PLATED STEEL NICKEL PLATED STEEL

BOARD LOCK: SEAL:

NICKEL PLATED BRASS

F08 FLEXIBLE ADHESIVE

MEETS IP67 STANDARDS

(SEE PAGE 3 FOR SEALING DETAILS)

684S5W5103LYYY

00 = 40 AMP POWER // NO BRACKET // STANDARD PCB TAILS

46 = 40 AMP POWER // #4-40 BRACKET // STANDARD PCB TAILS

62 = 40 AMP POWER // #4-40 BRACKET // 2.22mm PCB TAILS

1 = GOLD FLASH

ROHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. DRAWN:

M. SIGMON

DATE: 08/22/2011 UNITS = inches [mm]

DO NOT SCALE FROM DRAWING



SCALE: SHEET NTS 1 DWG NO.


684S5W5103L461


OF

3

REV

4





RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:

ATE: 08/22/2011 UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

NorComp DWG NO

SHEET OF


2


NTS DWG NO.

684S5W5103L461

3

REV





DETAIL A-A
SHOWN FOR REFERENCE ONLY

Rohs Compliant

M

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPAPATIS WITHOUT WITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE: 08/22/2011

UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: SHEET OF 3 3

DWG NO. 30.40 51445 4001 400

684S5W5103L461

REV