DESCRIPTION: 959 SERIES D-SUB BACKSHELL // 9P

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) 4-40 JACKSCREWS (1) HOUSING SCREWS
- (3) STRAIN RELIEF SCREWS
- (1) STRAIN RELIEF CLAMP
- (1) COVER PLATE

MATERIALS:

BACKSHELL:

BACKSHELL PLATING:

JACKSCREWS:

SPECIFICATIONS:

HOUSING SCREWS: STRAIN RELIEF SCREWS:

COVER PLATE:

STRAIN RELIEF CLAMP:


ENVIRONMENT:

OPERATING TEMPERATURE: -40°C TO +120°C


DIE-CAST ZINC ALLOY

ZINC PLATED STEEL

NICKEL OVER COPPER







ROHS COMPLIANT

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. DRAWN:

M. SIGMON

DATE: 05/12/2015 **GENERAL TOLERANCE** ANGLE (±5°) LINEAR = ± 0.015 [± 0.38]

UNITS = inch [mm]

NorComp

DO NOT SCALE FROM DRAWING OF REV

SCALE: SHEET NTS 1 DWG NO.

959-009-030R121

2