

PSL - Latching

1436966

<https://www.phoenixcontact.com/us/products/1436966>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Latching, depth: 63.8 mm, width: 9.7 mm, height: 8.7 mm, number of positions: 2, color: orange

Commercial data

Item number	1436966
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE29
Product key	BE244Z
GTIN	4063151814366
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	1.3 g
Customs tariff number	85389099
Country of origin	PL

Technical data

Product properties

Product type	Plug
Number of positions	2

Dimensions

Width	9.7 mm
Height	8.7 mm
Depth	63.8 mm

Material specifications

Color	orange (RAL 2003)
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

PSL - Latching

1436966

<https://www.phoenixcontact.com/us/products/1436966>



Classifications

ECLASS

ECLASS-13.0	27141190
-------------	----------

ETIM

ETIM 9.0	EC002848
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%