


FEMALE PLUG M12 STRAIGHT TO MALE PLUG M12 STRAIGHT



NOTES:









RATED VOLTAGE: 3, 4 contacts 250V per IEC 60664
5 contacts 60V per IEC 60664
5 contacts 250V per UL 2238
8 contacts 30V per IEC 60664

RATED CURRENT: 3, 4, 5 contacts 4A
8 contacts 2A

PROTECTION CLASS: IP 67

TEMPERATURE: -25°C / +85°C

CONTACTS POSITION FRONT VIEW:

	3 CONTACTS		4 CONTACTS		5 CONTACTS		8 CONTACTS	
FEMALE								
MALE								
CONNECTIONS	PIN	WIRE	PIN	WIRE	PIN	WIRE	PIN	WIRE
	1	BROWN	1	BROWN	1	BROWN	1	WHITE
	2	---	2	WHITE	2	WHITE	2	BROWN
	3	BLUE	3	BLUE	3	BLUE	3	GREEN
	4	BLACK	4	BLACK	4	BLACK	4	YELLOW
	5	---	5	---	5	GREY OR GREEN/YELLOW	5	GREY
							6	PINK
							7	BLUE
						8	RED	
CODING REQUIRED TO IEC 61076-2-101								

ENGINEERING NO. - NUMERICAL CODE (Available parts see PART LIST table. Other parts available upon request).

88X030XXXXXX

88=Micro-Change
M12x1
Double ended

Contacts:
3=3 Contacts
4=4 Contacts
5=5 Contacts
8=8 Contacts

Heads style:
030=Plug Female Straight
to Plug Male Straight

Cable type: See Table

Units:
M=Meter

Length
Examples:
005=0.5 unit
010=1 unit
100=10 units


Options

Overmold color:
Blank (Standard)=Black TPU
Blank=Yellow PVC for cables
A09, S19, S20, S26
Blank=Yellow TPE-E for cables
K03, K05
A=Grey / G=Black / Y=Yellow

Coupling Nut:
Blank (Standard)=Knurled Brass Ni Plated
1=Hexagonal Stainless steel
5=Knurled Derlin
7=Knurled Brass Ni Plated, Teflon Coated
Blank=7 for cables I20, I26, K03, K05, P82, S26
8=Type 316 stainless steel
9=Knurled / Hexagonal Brass Ni Plated SW13

H= 2 pcs. of I/D Carrier PVC Transparent
(Cables Ixx & P82 always with 2 pcs. of
I/D Carrier even if no H in Engineering No.)

COUPLING NUT
FEMALE MALE



CABLE LENGTH TOLERANCES		
OVER [mm]	UP TO AND INCLUDING [mm]	TOLERANCES [mm]
0	305	+19
305	915	+45
915	1830	+56
1830	3660	+89
3660	7320	+165
7320	14640	+317
14640	30500	+610
30500	>	+2% OF FINISHED LENGTH

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 1.0 °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.05

1 PLACE ± 0.3

0 PLACES ± 0.5

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#516585

EC NO: 823299
DRWN: VISHAH2
CHK'D: GGA
APPR: GGA

INITIAL REVISION:
DRWN: JMARSZALEK
APPR: RSILLER

2025/05/16
2025/05/29
2025/05/29
2016/09/19
2016/12/08

molex

CSE M12 XP AC FE STR MA STR XM DE

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

1200668165

DOC TYPE

PSD

DOC PART

000

REVISION

A9

MATERIAL NUMBER

SEE PART LIST

CUSTOMER

GENERAL MARKET

SHEET NUMBER

2 OF 5

THIRD ANGLE PROJECTION

DRAWING

SERIES

A3-SIZE

120066

CABLE INFORMATION(for more information see Cable Data Sheet).

CABLE TYPE	NO. OF WIRES	CROSS SECTION	CABLE JACKET	UL	CSA	STATIC: TEMP. / BENDING RADIUS	DYNAMIC: TEMP. / BENDING RADIUS	DRAG CHAIN	SHIELD
A09	4	22AWG	PVC YELLOW	UL 2661	I/II A/B 80°C/300V	-	-	-	-
B02	4	18AWG	PUR YELLOW	UL 20549	I/II A/B 80°C/300V	-	-	-	-
E52	3 / 4	0.34mm²	PVC GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	-
E57	5	0.34mm²	PVC GREY	-	-	-	-5°C to +70°C	-	-
I03	3 / 4 / 5	0.34mm²	PVC CEI GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	-
I20	3 / 4	0.34mm²	PVC CEI GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	YES
I26	5	0.34mm²	PVC CEI GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	YES
A8K03	4 / 5	18AWG	TPE YELLOW	UL ITC or PLTC	I/II A/B 90°C/300V	max 105°C	-	2 000 000 cycles, >15xO.D.	-
K05	3 / 4 / 5	22AWG	TPE YELLOW	UL ITC or PLTC	I/II A/B 90°C/300V	max 105°C	-	2 000 000 cycles, >15xO.D.	-
P20	3 / 4 / 5	0.34mm²	PUR BLACK LS0H	-	-	-30°C to +80°C	-	-	YES
P82	3 / 4 / 5	0.34mm²	PUR IRR ORANGE	-	-	-50°C to +105°C, >5xO.D.	-40°C to +105°C, >7.5xO.D.	-	-
S19	8	0.25mm²	PVC YELLOW	UL 2661/1569	C22.2 II A 105°C/300V	-30°C to +105°C, >10xO.D.	-15°C to +105°C, >15xO.D.	2 000 000 cycles, >15xO.D.	YES
S20	3 / 4 / 5	0.34mm²	PVC YELLOW	UL 2661/1731	C22.2 II A 105°C/300V	-30°C to +105°C	-	-	YES
S26	5	0.34mm²	PVC YELLOW	UL 2661/1731	C22.2 II A 105°C/300V	-30°C to +105°C	-	-	YES

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#516585				molex CSE M12 XP AC FE STR MA STR XM DE								
mm		1:1														
GENERAL TOLERANCES (UNLESS SPECIFIED)																
ANGULAR TOL		± 1.0 °		EC NO: 823299 DRWN: VISHAH2 2025/05/16 CHK'D: GGA 2025/05/29 APPR: GGA 2025/05/29				PRODUCT CUSTOMER DRAWING								
4 PLACES		±														
3 PLACES		±						INITIAL REVISION: DRWN: JMARSZALEK 2016/09/19 APPR: RSILLER 2016/12/08				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
2 PLACES		± 0.05										1200668165		PSD	000	A9
1 PLACE		± 0.3		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				MATERIAL NUMBER		CUSTOMER		SHEET NUMBER				
0 PLACES		± 0.5						SEE PART LIST		GENERAL MARKET		3 OF 5				
				THIRD ANGLE PROJECTION		DRAWING		SERIES								
						A3-SIZE		120066								

10	9	8	7	6	5	4	3	2	1
PART LIST									
Part No.			Engineering No.			Cable Length			
A09									
1200660166			883030A09M010			1m			
1200660261			884030A09M005			0.5m			
1200660262			884030A09M006			0.6m			
1200660266			884030A09M010			1m			
1200660269			884030A09M015			1.5m			
1200660271			884030A09M020			2m			
1200660273			884030A09M0208			2m			
1200660277			884030A09M030			3m			
1200669113			884030A09M0308			3m			
1200660286			884030A09M0508			5m			
1200660291			884030A09M070			7m			
1200660294			884030A09M080			8m			
1200660434			885030A09M050			5m			
B02									
1200660857			884030B02M020			2m			
1200660860			884030B02M030			3m			
1200660862			884030B02M050			5m			
1200660867			884030B02M100			10m			
E52									
1200071343			883030E52M003A			0.3m			
1200070956			883030E52M020A			2m			
1200071026			884030E52M010A			1m			
1200661434			884030E52M020A			2m			
1200071624			884030E52M030A			3m			
1200661472			884030E52M050A			5m			
1200070867			884030E52M100A			10m			
1200070653			884030E52M200A			20m			
I03									
1200070095			883030I03M003			0.3m			
1200070096			883030I03M006			0.6m			
1200070097			883030I03M010			1m			
1200669149			883030I03M010Y			1m			
1200070098			883030I03M020			2m			
1200668632			883030I03M020Y			2m			
1200070099			883030I03M030			3m			
1200668633			883030I03M030Y			3m			
1200668371			883030I03M040			4m			
1200070100			883030I03M050			5m			
1200668634			883030I03M050Y			5m			
1200070101			883030I03M100			10m			
1200070774			884030I03M006			0.6m			

