





WIRING DIAGRAM



VIEW FROM THE FRONT SIDE



VIEW FROM THE FRONT SIDE


NOTES:

1. MATERIAL: AS NOTED
2. FINISH: AS NOTED
3. PROTECTION: IP67 (WHEN MATED)
4. UL CERTIFICATION: UL LISTED, FILE NO. E152210
5. PART LIST AND PART NUMBER MATRIX - SEE SHEET 2
6. LABEL PRINTING ACC. STANDARD LABEL INSTRUCTION (SEE SHEET 2)

BILL OF MATERIAL

10	1	WRAP LABEL	VINYL	YELLOW
9	-	MOULDING MATERIAL	TPU	BLACK
8	1	MALE COUPLING NUT	ELECTROPHORETIC	BLACK
7	1	FEMALE COUPLING NUT	ELECTROPHORETIC	BLACK
6	1	FRICTION RING	NYLON	NATURAL
5	1	INSERT 5P MALE	ARNITEL	BLACK
4	1	INSERT 5P FEMALE	ARNITEL	BLACK
3	5	CONTACT MALE	BRASS	SELECTIVE GOLD OVER NICKEL
2	5	CONTACT FEMALE	BRASS	SELECTIVE GOLD OVER NICKEL
1	-	CABLE	TPU	GRAY
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH/COLOR

DOCUMENT STATUS	P1	RELEASE DATE	2023/04/27	12:11:51
-----------------	----	--------------	------------	----------




THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
FUNCTIONAL SYMBOLS FA=0 FE=0 FF=0	DIMENSION UNITS		SCALE		CURRENT REV DESC: NOTES AND CABLE SPEC UPDATED, LABEL PRINTING ADDED			molex CSE MC 5P A-SIZE FE STR WSOR MA STR XM DE					
	mm		1:1										
	GENERAL TOLERANCES (UNLESS SPECIFIED)												
DIVISIONAL SYMBOLS	ANGULAR TOL ± 1.0°		EC NO: 747270 DRWN: RSCHIEBER CHK'D: RSILLER APPR: RSILLER			2023/04/21 2023/04/27 2023/04/27			PRODUCT CUSTOMER DRAWING				
	4 PLACES ±												
	3 PLACES ±												
	2 PLACES ± 0.05												
	1 PLACE ± 0.3		INITIAL REVISION: DRWN: RSTONE APPR: JFMURPHY			2013/12/09 2013/12/16			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
	0 PLACES ± 0.5								SD-130010-030		PSD	001	B4
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER
				A3-SIZE	130010	SEE PART LIST	GENERAL MARKET		1 OF 2				

CABLE SPECIFICATION:

JACKET:
COLOR: GRAY
MATERIAL: TPU
CONDUCTOR:
STRANDING: 81x0.15 BARE COPPER
INSULATION DIAMETER: 2.40mm
INSULATION MATERIAL: TPE
RATING:
TEMPERATURE RATING: STATIC: -40 °C TO 90 °C
DYNAMIC: -25 °C TO 80 °C
VOLTAGE RATING: 600 V
CURRENT RATING: 10 A

PART NO. MATRIX



PART LIST

Lp	MOLEX PN	ENGINEERING No	L [mm]	Lp	MOLEX PN	ENGINEERING No	L [mm]
1	1300108044	115030B35M010	1000	36	1300108141	115030B35M850	85000
2	1300108045	115030B35M020	2000	37	1300108142	115030B35M900	90000
3	1300108046	115030B35M030	3000	38	1300108143	115030B35M950	95000
4	1300108047	115030B35M050	5000	39			
5	1300108048	115030B35M100	10000	40			
6	1300108049	115030B35M150	15000	41			
7	1300108050	115030B35M200	20000	42			
8	1300108107	115030B35M005	500	43			
9	1300108109	115030B35M015	1500	44			
10	1300108111	115030B35M025	2500	45			
11	1300108113	115030B35M035	3500	46			
12	1300108114	115030B35M040	4000	47			
13	1300108116	115030B35M060	6000	48			
14	1300108117	115030B35M080	8000	49			
15	1300108119	115030B35M120	12000	50			
16	1300108121	115030B35M180	18000	51			
17	1300108122	115030B35M200	20000	52			
18	1300108123	115030B35M230	23000	53			
19	1300108124	115030B35M250	25000	54			
20	1300108125	115030B35M270	27000	55			
21	1300108126	115030B35M300	30000	56			
22	1300108127	115030B35M340	34000	57			
23	1300108128	115030B35M380	38000	58			
24	1300108129	115030B35M400	40000	59			
25	1300108130	115030B35M420	42000	60			
26	1300108131	115030B35M460	46000	61			
27	1300108132	115030B35M500	50000	62			
28	1300108133	115030B35M540	54000	63			
29	1300108134	115030B35M570	57000	64			
30	1300108135	115030B35M600	60000	65			
31	1300108136	115030B35M610	61000	66			
32	1300108137	115030B35M650	65000	67			
33	1300108138	115030B35M700	70000	68			
34	1300108139	115030B35M750	75000	69			
35	1300108140	115030B35M800	80000	70			

LABEL PRINTING




TABLE OF LENGTH TOLERANCES		
OVER	UP TO AND INCLUDING	TOLERANCE
0	305	+19
305	915	+45
915	1830	+56
1830	3660	+89
3660	7320	+165
7320	14640	+317
14640	30500	+610
30500	>	+2% OF LENGTH

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
= 0 = 0 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: NOTES AND CABLE SPEC UPDATED, LABEL PRINTING ADDED			molex						
	mm		1:1											
	GENERAL TOLERANCES (UNLESS SPECIFIED)					EC NO: 747270 DRWN: RSCHIEBER2023/04/21 CHK'D: RSILLER2023/04/27 APPR: RSILLER2023/04/27			CSE MC 5P A-SIZE FE STR WSOR MA STR XM DE					
	ANGULAR TOL ± 1.0 °													
	4 PLACES		±		INITIAL REVISION: DRWN: RSTONE2013/12/09 APPR: JFMURPHY2013/12/16			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION		
3 PLACES		±		SD-130010-030				PSD	001	B4				
2 PLACES		± 0.05												
1 PLACE		± 0.3												
0 PLACES		± 0.5												
DIVISIONAL SYMBOLS	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
							A3-SIZE	130010	SEE PART LIST		GENERAL MARKET		2 OF 2	