




COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



PCB hole pattern, mounting side



5	2	Clinch nut	MW 4-40 / Steel	tin plated
4	2	Bracket	F1080-13B / Steel	tin plated
3	8	Coaxial contact	FME008P102R	50Ω
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C to +130°C) acc. UL94V-0	green
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class
FUNCTIONAL SYMBOLS				
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
DIMENSION UNITS		SCALE	MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-m	
mm		2:1		
			CURRENT REVISION	
			DRWN: DRAWN BY	msteinbrueck 04-10-2022
			APPR: APPR BY	mteubel 03-04-2023
			INITIAL REVISION	
			DRWN: DRAWN BY	mpostulka 30-05-2008
			APPR: APPR BY	MJobst 30-05-2008
2	24193			
1				
REV.	CH.-NO.			
REPLACEMENT FOR:		FRIST ANGLE PROJECTION	DRAWING	
			A3-SIZE	
			DOCUMENT NUMBER	
			FM8W8P-0739	
			CUSTOMER	
			GENERAL MARKET	
			SHEET NUMBER	1 OF 1