







MATERIALS AND FINISHES:

BODY, JAM NUT: BRASS
PLATING: SEE TABLE

CENTER CONTACT: BRASS
PLATING: SEE TABLE

INSULATOR: TEFLON


LOCK WASHER: PHOSPHOR BRONZE
PLATING: SEE TABLE



73251-2773	NICKEL 100μ-in MIN	GOLD 10μ-in MIN	OMIT	OMIT
73251-2772	GOLD 5μ-in MIN		OMIT	OMIT
73251-2771	GOLD 5μ-in MIN		89611-0529, GOLD 1μ-in MIN	89610-1143, GOLD 1μ-in MIN
73251-2770	NICKEL 100μ-in MIN		89611-0527, NICKEL 100μ-in MIN	89610-1141, NICKEL 100μ-in MIN
PART NO.	BODY	CONTACT	JAM NUT	LOCK WASHER

73251-2773	TRAY	895420620
73251-2772		
73251-2771		
73251-2770		
PART NO.	PACKAGING	PACKING SPEC

PS-89675-368	SOLDER SPEC PROFILE
PS-89675-346	ELECTRO/MECH PERFORM.
SPECIFICATION	DESCRIPTION

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC: ADDED PLATING & PKG NOTE & SPEC & TOLERANCE PER EWR16158-A & B			molex							
	INCH NTS		SMA JACK, R/A, PCB REVERSE POLARITY, 50 OHM EWR-2827, SMA-J/RP/PCB												
	GENERAL TOLERANCES (UNLESS SPECIFIED)														
	ANGULAR TOL ± 2°														
	4 PLACES		± 0.00500		PRODUCT SALES DRAWING										
	3 PLACES		± 0.0100												
	2 PLACES		±												
	1 PLACE		±												
	0 PLACES		±		DOCUMENT NUMBER			DOC TYPE		DOC PART	REVISION				
DIVISIONAL SYMBOLS		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				C-SIZE		73251		SEE TABLE		SPECTRAL RESPONSE		1 OF 1			
				STATUS: Design Approved		DRWN: Cela Wei		2023-11-10		DOC-73251-277		PSD		001	A7
				CHK'D: Kerrie Chen		2024-02-01		2024-02-01		CUSTOMER		SPECTRAL RESPONSE		1 OF 1	
APPR: Darry Cheng															

molex

SMA JACK, R/A, PCB
REVERSE POLARITY, 50 OHM EWR-2827,
SMA-J/RP/PCB

PRODUCT SALES DRAWING

DOCUMENT NUMBER
SD-73251-277
DOC TYPE
PSD
DOC PART
001
REVISION
A7