










SECTION A-A



HOLES ON SOME
TOOLED VERSIONS




NOTES:

1. MATERIAL:
HOUSING: PA 66 , UL94 V-0 750°C GWT NO FLAME
TERMINAL: BRASS 0.80REF. THICK
PLATING: OPTIONAL (SEE CHARTS SHEETS 3-11)
TIN PLATING OPTION : 3µm TIN OVER
1.27µm NICKEL ALL AREAS.
SELECTIVE SILVER
CONTACT AREA : 2µm SILVER OVER 1.27µm
NICKEL. ALL OTHER AREAS FLASH OF SILVER 0.10µm
2. PRODUCT CONFORMS TO SPECIFICATION PS-99020-0037/39
3. MATES WITH MOLEX 91338, 90833, 90835, 91777, 91778, 91954, 92000 & 91779
4. PARTS PACKED IN TRAYS OPTION C SEE PK-90858-001 FOR PACKAGING INFORMATION
5. PLATED THRU HOLE
6. RECOMMENDED PCB THICKNESS: 1.5 mm REF



CCT	DIM A	DIM B	DIM C	TOL
2	5.00	10.20	12.30	+/-0.30
3	10.00	15.20	17.30	
4	15.00	20.20	22.30	
5	20.00	25.20	27.30	
6	25.00	30.20	32.30	
7	30.00	35.20	37.30	
8	35.00	40.20	42.30	
9	40.00	45.20	47.30	
10	45.00	50.20	52.30	
11	50.00	55.20	57.30	
12	55.00	60.20	62.30	

RECOMMENDED PCB LAYOUT


P.C.B. POLARISATION OPTION "A"





P.C.B.
OPTION "A"




P.C.B. POLARISATION OPTION "B"
(FOR REVERSE FOOTPRINT)





P.C.B.
OPTION "B"



P.C.B. POLARISATION OPTION "C"
(STRAIGHT PINS)




P.C.B.
OPTION "C"





FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex						
	mm		4:1											
	FA = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)				RAST 5 R.A. HDR PA 66 HOUSING							
	FC = 0		ANGULAR TOL ± 2.0°											
	FE = 0		EC NO: 749359											
	4 PLACES		±		DRWN: RAHULH3					2023/05/12				
	3 PLACES		±		CHK'D: RAHULH3					2023/05/12				
	DIVISIONAL SYMBOLS	2 PLACES		± 0.1		APPR: MRAMAKRISHNA		2023/05/12		PRODUCT CUSTOMER DRAWING				
		1 PLACE		± 0.2		INITIAL REVISION:		DRWN: AKABADI					2017/09/08	
0 PLACES		±		APPR: BRUTTLE		2017/11/10		DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
				A1-SIZE		93003		SEE SHEET 3-11		GENERAL MARKET		1 OF 11		



NON-POTABLE HEADER, LOWER SIDE LATCH OPTION





POTABLE HEADER OPTION WITH LOWER SIDE LATCH
P/N 93003-0070 - 2CCT ONLY
CONTACT ENGINEERING FOR LARGER CIRCUIT SIZES





P.C.B.
OPTION "A"




P.C.B.
OPTION "B"




P.C.B.
OPTION "C"



P.C.B. POLARISATION
OPTION "A"
PCB VIEW IS FROM
SOLDER SIDE



P.C.B. POLARISATION
OPTION "B"
PCB VIEW IS FROM
SOLDER SIDE



P.C.B. POLARISATION
OPTION "C"
PCB VIEW IS FROM
SOLDER SIDE

FUNCTIONAL SYMBOLS DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																				
	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex RAST 5 R.A. HDR PA 66 HOUSING											
	mm		4:1																		
	GENERAL TOLERANCES (UNLESS SPECIFIED)					EC NO: 749359 DRWN: RAHULH32023/05/12 CHK'D: RAHULH32023/05/12 APPR: MRAMAKRISHNA2023/05/12					PRODUCT CUSTOMER DRAWING										
	ANGULAR TOL ± 2.0°																				
	4 PLACES		±																		
	3 PLACES		±			INITIAL REVISION: DRWN: AKABADI2017/09/08 APPR: BRUTTLE2017/11/10					DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION					
	2 PLACES		± 0.1								930030001		PSD		000	B1					
	1 PLACE		± 0.2																		
	0 PLACES		±			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
					 						A1-SIZE		93003		SEE SHEET 3-11		GENERAL MARKET		2 OF 11		

LOWER SIDE LATCH

POSITION WINDOWS

1a 1b 2a 2b 3a 3b 4a 4b

01c d20 03c d30 04c d40

CODING WINDOWS

LATCH (POSITION 1/2)

KEYING, CODING & LATCH POSITION
(4CCT EXAMPLE SHOWN)
VIEW INMATING DIRECTION

Diagram illustrating the Keying, Coding & Latch Position for a 4CCT (4-Column Code Table) example, viewed in the Inmating Direction.

The diagram shows four columns labeled Cct 1, Cct 2, Cct 3, and Cct 4. Each column has a POSITION WINDOW (1a, 1b, 2a, 2b, 3a, 3b, 4a, 4b) and a CODING WINDOW (01c, d20, 03c, d30, 04c, d40). A LATCH (POSITION 1/2) is shown at the bottom center.

KEYING, CODING & LATCH POSITION
(4CCT EXAMPLE SHOWN)
VIEW INMATING DIRECTION

DOCUMENT STATUS	P1	RELEASE DATE	2023/05/12	09:50:23
-----------------	----	--------------	------------	----------





2 CIRCUIT

SEE CODE DESIGNATION TABLE FOR NUMBERING
FORMAT WHEN ADDING NEW PART NUMBERS

P.C.B.
POLARISATION
OPTION

TOP SIDE
LATCH

POTABLE HOUSING

PART NO. (TIN)	TERM NO. (TIN)	MOLEX HOUSING NO.	TERMINAL VOID POSITION	UNBLOCKED POSITION KEYS	UNBLOCKED CODING KEYS	LATCH POSITION	CONFIGURATION (SEE NOTES)	LUMBERG K REF	TERM NO. (SILVER)	PART NO. (SILVER)	POLARISATION OPTION	LATCH	HOUSING
93003-0064	91703-0005/8	93002-0024	NONE	ALL	ALL	1/2		K00	91703-0006/9	93003-0470	A	YES	NO
93003-0065	91703-0005/8	93002-0003	NONE	1a 2b	01c	1/2		K02	91703-0006/9	93003-0469	A	NO	
93003-0066	91703-0005/8	93002-0003	NONE	1a 2b	01c	1/2		K02	91703-0006/9	93003-0468	B	NO	
93003-0067	91703-0005/8	93002-0035	NONE	1b 2a 2b	01c d20	1/2		K78	91703-0006/9	93003-0467	A	YES	
93003-0068	91703-0005/8	93002-0002	NONE	1b 2a	01c d20	1/2		K01	91703-0006/9	93003-0466	A	NO	
93003-0069	91703-0005/8	93002-0005	NONE	2a	01c d20	1/2		K03	91703-0006/9	93003-0465	A	NO	
93003-0070	91703-0005/8	93228-0008	NONE	1a 2b	NONE	1/2		---	91703-0006/9	93003-0464	A	NO	YES
93003-0071	91703-0005	93002-0028	NONE	1a 2a 2b	01c d20	1/2		---	91703-0006	93003-0463	C	YES	NO
93003-0072	91703-0005/8	93002-0026	NONE	2a 2b	01c	1/2		---	91703-0006/9	93003-0462	A	YES	NO

B

[illegible]




















DOCUMENT STATUS	P1	RELEASE DATE	2023/05/12	09:50:23
-----------------	----	--------------	------------	----------

3 CIRCUIT

SEE CODE DESIGNATION TABLE FOR NUMBERING
FORMAT WHEN ADDING NEW PART NUMBERS

P.C.B.
POLARISATION
OPTION

TOP SIDE
LATCH

93003-0502	91703-0005/8	93002-1000	NONE	1b	01c d20	1/2		K01	91703-0006/9	93003-1249	A	YES
93003-0508	91703-0005/8	93002-1001	NONE	1a	03c	1/2		K04	91703-0006/9	93003-1248	A	YES
93003-0528	91703-0005/8	93002-1002	NONE	1a 1b	d30	1/2		K05	91703-0006/9	93003-1247	A	YES
93003-0512	91703-0005/8	93002-1003	NONE	1a 3b	01c	1/2		K06	91703-0006/9	93003-1246	A	YES
93003-0513	91703-0005/8	93002-1004	NONE	1b	d20 03c	1/2		K09	91703-0006/9	93003-1245	A	YES
93003-0529	91703-0005/8	93002-1005	NONE	1b 2a 2b	d30	1/2		K33	91703-0006/9	93003-1244	A	YES
93003-0530	91703-0005/8	93002-1006	NONE	2b	d20	1/2		K08	91703-0006/9	93003-1243	A	YES
93003-0526	91703-0005/8	93002-1007	NONE	ALL	d10 d30	2/3		K38	91703-0006/9	93003-1242	A	YES
93003-0527	91703-0005/8	93002-1008	NONE	ALL	d20	1/2		K40	91703-0006/9	93003-1241	A	YES
93003-0531	91703-0005/8	93002-1014	NONE	ALL	ALL	1/2		K00	91703-0006/9	93003-1240	A	YES
93003-0532	91703-0005/8	93002-1020	NONE	3b	01c d30	1/2		K37	91703-0006/9	93003-1239	A	YES
93003-0533	91703-0005/8	93002-1021	NONE	1b 3a	01c	1/2		K03	91703-0006/9	93003-1238	A	NO
93003-0534	91703-0005/8	93002-1000	CCT 2	1b	01c d20	1/2		K--	91703-0006/9	93003-1237	A	YES
93003-0535	91703-0005/8	93002-1024	CCT 2	3b	01c 03c	1/2		K--	91703-0006/9	93003-1236	A	YES
93003-0536	91703-0005	93002-1011	CCT 2	3b	01c d30	2/3		K--	91703-0006	93003-1235	C	YES
93003-0537	91703-0005	93002-1000	NONE	1b	01c d20	1/2		K--	91703-0006	93003-1234	C	YES
93003-0538	91703-0005	93002-1036	NONE	NONE	d10 02c d30	2/3		K--	91703-0006	93003-1233	C	YES
93003-0539	91703-0005/8	93002-1000	NONE	1b	01c d20	1/2		K01	91703-0006/9	93003-1232	A	NO
93003-0540	91703-0005/8	93002-1039	NONE	1b 2a	d20	1/2		--	91703-0006/9	93003-1231	A	NO

B

[illegible]

DOCUMENT STATUS	P1	RELEASE DATE	2023/05/12	09:50:23
-----------------	----	--------------	------------	----------

18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
4 CIRCUIT											SEE CODE DESIGNATION TABLE FOR NUMBERING FORMAT WHEN ADDING NEW PART NUMBERS	P.C.B. POLARISATION OPTION	TOP SIDE LATCH				
PART NO. (TIN)	TERM NO. (TIN)	MOLEX HOUSING NO.	TERMINAL VOID POSITION	UNBLOCKED POSITION KEYS	UNBLOCKED CODING KEYS	LATCH POSITION	CONFIGURATION (SEE NOTES)	LUMBERG K REF	TERM NO. (SILVER)	PART NO. (SILVER)							
93003-1254	91703-0005/8	93002-2000	NONE	1b	03c d40	1/2 3/4		K01	91703-0006/9	93003-1999	A	YES					
93003-1264	91703-0005/8	93002-2001	NONE	1a 4b	d40	1/2 3/4		K03	91703-0006/9	93003-1997	A	YES					
93003-1265	91703-0005/8	93002-2002	NONE	2a 4b	d20	1/2 3/4		K07	91703-0006/9	93003-1996	A	YES					
93003-1267	91703-0005/8	93002-2003	NONE	1b 2a 3a 4b	01c d40	1/2 3/4		K37	91703-0006/9	93003-1994	A	YES					
93003-1278	91703-0005/8	93002-2004	NONE	1a 2b 4b	01c 03c d40	1/2 3/4		K44	91703-0006/9	93003-1988	A	YES					
93003-1279	91703-0005/8	93002-2005	NONE	1a 3a 3b	01c d20 d40	1/2 3/4		K32	91703-0006/9	93003-1987	A	YES					
93003-1280	91703-0005/8	93002-2006	NONE	1b 2a 4b	01c d20 03c	1/2 3/4		K61	91703-0006/9	93003-1986	A	YES					
93003-1281	91703-0005/8	93002-2007	NONE	1a 3a	d40	1/2 3/4		K06	91703-0006/9	93003-1985	A	YES					
93003-1282	91703-0005/8	93002-2008	NONE	1a 2b 3b 4a	01c 03c d40	1/2 3/4		K65	91703-0006/9	93003-1984	A	YES					
93003-1266	91703-0005/8	93002-2009	NONE	2a 4b	d20 03c	1/2 3/4		K30	91703-0006/9	93003-1995	A	YES					
93003-1276	91703-0005/8	93002-2010	NONE	3b	d30	2/3		K04	91703-0006/9	93003-1989	A	YES					
93003-1283	91703-0005/8	93002-2018	NONE	ALL	ALL	1/2 3/4		K00	91703-0006/9	93003-1983	A	YES					
93003-1284	91703-0005/8	93002-2022	NONE	1b	03c	1/2 3/4		N/A	91703-0006/9	93003-1982	A	YES					
93003-1285	91703-0005/8	93002-2024	NONE	ALL	03c d40	1/2 3/4		N/A	91703-0006/9	93003-1981	A	YES					
93003-1286	91703-0005/8	93002-2000	NONE	1b	03c d40	1/2 3/4		K01	91703-0006/9	93003-1980	B	YES					
93003-1287	91703-0005/8	93002-2025	CCT 2	1a 3a 3b 4a 4b	03c d40	1/2 3/4		K--	91703-0006/9	93003-1979	A	YES					
93003-1288	91703-0005/8	93002-2000	NONE	1b	03c d40	1/2 3/4		K01	91703-0006/9	93003-1978	A	NO					
93003-1289	91703-0005/8	93002-2032	NONE	1a 2b 3b 4a	d20 03c d40	1/2 3/4		K86	91703-0006/9	93003-1977	A	YES					

FUNCTIONAL SYMBOLS

= 0

= 0

= 0

DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

SCALE

CURRENT REV DESC:

mm

1:1

EC NO: 749359
DRWN: RAHULH3
CHK'D: RAHULH3
APPR: MRAMAKRISHNA

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 2.0 °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.1

1 PLACE ± 0.2

0 PLACES ±

INITIAL REVISION:

DRWN: AKABADI
APPR: BRUTTLE

2023/05/12
2023/05/12
2023/05/12

2017/09/08
2017/11/10

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

SERIES

A1-SIZE

93003

DOCUMENT NUMBER

CUSTOMER

SHEET NUMBER

930030001

PSD

000

B1

SEE SHEET 3-11

GENERAL MARKET

6 OF 11

DOCUMENT STATUS

P1

RELEASE DATE

2023/05/12 09:50:23

18

17

16

15

14

13

12

11

10

9

8

7

6

5

4

3

2




1

4 CIRCUIT


SEE CODE DESIGNATION TABLE FOR NUMBERING
FORMAT WHEN ADDING NEW PART NUMBERS

P.C.B.
POLARISATION
OPTION

TOP SIDE
LATCH

PART NO. (TIN)	TERM NO. (TIN)	MOLEX HOUSING NO.	TERMINAL VOID POSITION	UNBLOCKED POSITION KEYS	UNBLOCKED CODING KEYS	LATCH POSITION	CONFIGURATION (SEE NOTES)	LUMBERG K REF	TERM NO. (SILVER)	PART NO. (SILVER)	POLARISATION OPTION	LATCH
93003-1290	91703-0005/8	93002-2000	CCT 3	1b	03c d40	1/2 3/4		K01	91703-0006/9	93003-1976	A	YES
93003-1291	91703-0005/8	93002-2018	NONE	ALL	ALL	1/2 3/4		K00	91703-0006/9	93003-1975	A	NO
93003-1292	91703-0005/8	93002-2043	NONE	2a 2b 3b 4b	01c d40	1/2 3/4		---	91703-0006/9	93003-1974	A	YES
93003-1293	91703-0005/8	93002-2045	NONE	1b 2b 4a 4b	d20 03c	1/2 3/4		K296	91703-0006/9	93003-1973	A	NO
93003-1294	91703-0005	93002-2000	NONE	1b	03c d40	1/2 3/4		K**	91703-0006	93003-1972	C	YES
93003-1295	91703-0005/8	93002-2000	NONE	1b	03c d40	1/2 3/4		K**	91703-0006/9	93003-1971	A	YES
93003-1296	91703-0005/8	93002-2048	NONE	1a 2b 4a	01c d40	1/2 3/4		--	91703-0006/9	93003-1970	A	YES

B

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
SYMBOLS FA = 0 FE = 0 FB = 0 DIVISIONAL SYMBOLS	DIMENSION UNITS mm SCALE 1:1 GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 2.0 ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.1 1 PLACE ± 0.2 0 PLACES ±
CURRENT REV DESC: EC NO: 749359 DRWN: RAHULH3 CHK'D: RAHULH3 APPR: MRAMAKRISHNA 2023/05/12 2023/05/12 2023/05/12	
RAST 5 R.A. HDR PA 66 HOUSING	
PRODUCT CUSTOMER DRAWING	
DOCUMENT NUMBER 930030001	DOC TYPE PSD
DOC PART 000	REVISION B1
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION 
DRAWING A1-SIZE	SERIES 93003
MATERIAL NUMBER SEE SHEET 3-11	CUSTOMER GENERAL MARKET
SHEET NUMBER 7 OF 11	

DOCUMENT STATUS	P1	RELEASE DATE	2023/05/12	09:50:23
-----------------	----	--------------	------------	----------

18																		17																		16																		15																		14																		13																		12																		11																		10																		9																		8																		7																		6																		5																		4																		3																		2																		1																	
5 CIRCUIT																																																																																																																																																																																						SEE CODE DESIGNATION TABLE FOR NUMBERING FORMAT WHEN ADDING NEW PART NUMBERS																		P.C.B. POLARISATION OPTION																		TOP SIDE LATCH																																																																																																									
PART NO. (TIN)																		TERM NO. (TIN)																		MOLEX HOUSING NO.																		TERMINAL VOID POSITION																		UNBLOCKED POSITION KEYS																		UNBLOCKED CODING KEYS																		LATCH POSITION																		CONFIGURATION (SEE NOTES)																		LUMBERG K REF																		TERM NO. (SILVER)																		PART NO. (SILVER)																																																																																																																																															
93003-2000																		91703-0005/8																		93002-3000																		NONE																		1a 5b																		01c d30																		1/2 2/3																																				K01																		91703-0006/9																		93003-2749																		A																		YES																																																																																																											
93003-2001																		91703-0005/8																		93002-3001																		NONE																		1a 3a																		01c d30																		1/2 4/5																																				K30																		91703-0006/9																		93003-2748																		A																		YES																																																																																																											
93003-2002																		91703-0005/8																		93002-3002																		NONE																		1a 5b																		01c d20 03c d50																		1/2 3/4																																				K31																		91703-0006/9																		93003-2747																		A																		YES																																																																																																											
93003-2003																		91703-0005/8																		93002-3003																		NONE																		1b 2a 3b 5a																		01c 03c																		1/2 3/4																																				K35																		91703-0006/9																		93003-2746																		A																		YES																																																																																																											
93003-2023																		91703-0005/8																		93002-3004																		NONE																		1a 2a 2b 4b 5b																		01c d30 04c d50																		1/2 2/3 4/5																																				K36																		91703-0006/9																		93003-2732																		A																		YES																																																																																																											
93003-2024																		91703-0005/8																		93002-3005																		NONE																		2a																		01c d50																		2/3 4/5																																				K43																		91703-0006/9																		93003-2731																		A																		YES																																																																																																											
93003-2025																		91703-0005/8																		93002-3006																		NONE																		2a 4b																		01c d20 d40																		1/2 3/4																																				K44																		91703-0006/9																		93003-2730																		A																		YES																																																																																																											
93003-2026																		91703-0005/8																		93002-3007																		NONE																		2b																		d20																		1/2 4/5																																				K02																		91703-0006/9																		93003-2729																		A																		YES																																																																																																											
93003-2027																		91703-0005/8																		93002-3008																		NONE																		4b 5a																		01c d30 04c d50																		1/2 4/5																																				K45																		91703-0006/9																		93003-2728																		A																		YES																																																																																																											
93003-2028																		91703-0005/8																		93002-3009																		NONE																		NONE																		01c d40																		1/2 3/4																																				K46																		91703-0006/9																		93003-2727																		A																		YES																																																																																																											
93003-2029																		91703-0005/8																		93002-3032																		NONE																		1a 4b																		d30																		1/2 4/5																																				K04																		91703-0006/9																		93003-2726																		A																		YES																																																																																																											
93003-2030																		91703-0005/8																		93002-3011																		NONE																		1a 5b																		d20 d40																		1/2 3/4																																				K77																		91703-0006/9																		93003-2725																		A																		YES																																																																																																											
93003-2005																		91703-0005/8																		93002-3012																		NONE																		1b 2b 4a																		d20 d30 d50																		1/2 4/5																																				K40																		91703-0006/9																		93003-2744																		A																		YES																																																																																																											
93003-2016																		91703-0005/8																		93002-3013																		NONE																		3b 4a 5b																		01c d30 d50																		2/3 4/5																																				K47																		91703-0006/9																		93003-2738																		A																		YES																																																																																																											
93003-2018																		91703-0005/8																		93002-3014																		NONE																		1a 4b																		01c																		1/2 3/4																																				K48																		91703-0006/9																		93003-2736																		A																		YES																																																																																																											
93003-2020																		91703-0005/8																		93002-3015																		NONE																		1a 5b																		d30 04c																		2/3																																				K50																		91703-0006/9																		93003-2734																		A																		YES																																																																																																											
93003-2021																		91703-0005/8																		93002-3016																		NONE																		1b 2a 4a																		01c 04c d50																		1/2 4/5																																				K51																		91703-0006/9																		93003-2733																		A																		YES																																																																																																											
93003-2022																		91703-0005/8																		93002-3017																		NONE																		2b 3b 4a																		01c d20 d40																		1/2 3/4																																				K52																		91703-0006/9																		93003-2735																		A																		YES																																																																																																											
93003-2031																		91703-0005/8																		93002-3024																		NONE																		ALL																		ALL																		1/2 3/4																																				K00																		91703-0006/9																		93003-2724																		A																		YES																																																																																																											
93003-2032																		91703-0005/8																		93002-3025																		CCT 3																		2b																		d30																		1/2 4/5																																				N/A																		91703-0006/9																		93003-2723																		B																		YES																																																																																																											
93003-2033																		91703-0005/8																		93002-3027																		CCT 2																		2b																		01c d20 03c d30 04c d50																		1/2 4/5																																				N/A																		91703-0006/9																		93003-2722																		A																		YES																																																																																																											
93003-2034																		91703-0005/8																		93002-3028																		CCT 3																		2b																		01c d20 03c 04c d50																		1/2 4/5																																				N/A																		91703-0006/9																		93003-2721																		A																		YES																																																																																																											

DOCUMENT STATUS																		P1																		RELEASE DATE																		2023/05/12																		09:50:23																																																																																																																																																																																																																																																											
18																		17																		16																		15																		14																		13																		12																		11																		10																		9																		8																		7																		6																		5																		4																		3																		2																		1																	

18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
6 CIRCUIT											SEE CODE DESIGNATION TABLE FOR NUMBERING FORMAT WHEN ADDING NEW PART NUMBERS	P.C.B. POLARISATION OPTION	TOP SIDE LATCH				
PART NO. (TIN)	TERM NO. (TIN)	MOLEX HOUSING NO.	TERMINAL VOID POSITION	UNBLOCKED POSITION KEYS	UNBLOCKED CODING KEYS	LATCH POSITION	CONFIGURATION (SEE NOTES)	LUMBERG K REF	TERM NO. (SILVER)	PART NO. (SILVER)							
93003-2753	91703-0005/8	93002-4000	NONE	1b	03c d60	1/2 4/5		K01	91703-0006/9	93003-3499	A	YES					
93003-2754	91703-0005/8	93002-4001	NONE	1a 3b 4b	01c d50 06c	1/2 4/5		K30	91703-0006/9	93003-3498	A	YES					
93003-2755	91703-0005/8	93002-4002	NONE	1a 1b 2b 3a 3b 4b	d30 04c d50	1/2 2/3 4/5		K37	91703-0006/9	93003-3497	A	YES					
93003-2756	91703-0005/8	93002-4003	NONE	1a 1b 4a 4b	d10 d50	2/3 4/5		K39	91703-0006/9	93003-3496	A	YES					
93003-2757	91703-0005/8	93002-4004	NONE	2a 4b 5a 6b	d20 03c 05c	1/2 3/4 5/6		K42	91703-0006/9	93003-3495	A	YES					
93003-2758	91703-0005/8	93002-4005	NONE	1a 2b 3a 3b 5b 6b	01c d40 d60	1/2 3/4 5/6		K43	91703-0006/9	93003-3494	A	YES					
93003-2759	91703-0005/8	93002-4006	NONE	1b 2a 3a 4b 5a 5b 6b	01c 03c d60	1/2 3/4 5/6		K44	91703-0006/9	93003-3493	A	YES					
93003-2760	91703-0005/8	93002-4007	NONE	2b	d20 d60	1/2 5/6		K46	91703-0006/9	93003-3492	A	YES					
93003-2761	91703-0005/8	93002-4008	NONE	2b 3b 4a	01c d50 06c	1/2 4/5		K36	91703-0006/9	93003-3491	A	YES					
93003-2762	91703-0005/8	93002-4009	NONE	1b 4b	d20 03c d50 06c	1/2 4/5		K58	91703-0006/9	93003-3486	A	YES					
93003-2764	91703-0005/8	93002-4010	NONE	1a 2b 3b 4a 6b	01c 03c d40 05c d60	1/2 3/4 5/6		K59	91703-0006/9	93003-3485	A	YES					
93003-2765	91703-0005/8	93002-4011	NONE	1a 2b 4a 6b	01c d40	1/2 3/4 5/6		K62	91703-0006/9	93003-3484	A	YES					
93003-2763	91703-0005/8	93002-4029	NONE	1b 2b 3b	01c 05c d60	1/2 3/4 5/6		K04	91703-0006/9	93003-3490	A	YES					
93003-2766	91703-0005/8	93002-4013	NONE	1b	d20 03c	1/2 4/5		K55	91703-0006/9	93003-3489	A	YES					
93003-2767	91703-0005/8	93002-4014	NONE	1b 2a 3a 5a 5b	01c d20 03c d40 d60	1/2 3/4 5/6		K56	91703-0006/9	93003-3488	A	YES					
93003-2771	91703-0005/8	93002-4015	NONE	1a 3a 3b 5b 6a	01c d20 d40 05c d60	1/2 3/4 5/6		K60	91703-0006/9	93003-3487	A	YES					
93003-2772	91703-0005/8	93002-4018	NONE	ALL	ALL	1/2 4/5		K00	91703-0006/9	93003-3483	A	YES					
93003-2773	91703-0005/8	93002-4024	NONE	1b 2a 2b 3a 6a 6b	d20 04c d60	1/2 5/6		K29	91703-0006/9	93003-3482	A	NO					

FUNCTIONAL SYMBOLS DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC:												
	mm		1:1														
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 749359 DRWN: RAHULH3 CHK'D: RAHULH3 APPR: MRAMAKRISHNA INITIAL REVISION: DRWN: AKABADI APPR: BRUTTLE												
	ANGULAR TOL		± 2.0 °														
	4 PLACES		±														
	3 PLACES		±														
	2 PLACES		± 0.1														
	1 PLACE		± 0.2														
	0 PLACES		±														
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING A1-SIZE		SERIES 93003		DOCUMENT NUMBER 930030001		DOC TYPE PSD		DOC PART 000		REVISION B	
										MATERIAL NUMBER SEE SHEET 3-11		CUSTOMER GENERAL MARKET		SHEET NUMBER 9 OF 11			

DOCUMENT STATUS	P1	RELEASE DATE	2023/05/12	09:50:23													
18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1

18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
7 CIRCUIT											SEE CODE DESIGNATION TABLE FOR NUMBERING FORMAT WHEN ADDING NEW PART NUMBERS	P.C.B. POLARISATION OPTION	TOP SIDE LATCH				
PART NO. (TIN)	TERM NO. (TIN)	MOLEX HOUSING NO.	TERMINAL VOID POSITION	UNBLOCKED POSITION KEYS	UNBLOCKED CODING KEYS	LATCH POSITION	CONFIGURATION (SEE NOTES)	LUMBERG K REF	TERM NO. (SILVER)	PART NO. (SILVER)							
93003-3500	91703-0005/8	93002-5000	NONE	NONE	03c d40 07c	1/2 5/6		K01	91703-0006/9	93003-4220	A	YES					
93003-3512	91703-0005/8	93002-5001	NONE	3a 4a	d30 d70	1/2 5/6		K30	91703-0006/9	93003-4248	A	YES					
93003-3504	91703-0005/8	93002-5002	NONE	2b	d20 d60	1/2 5/6		K32	91703-0006/9	93003-4247	A	YES					
93003-3513	91703-0005/8	93002-5003	NONE	1a 1b 3a 4b 5a	01c 07c	1/2 3/4 5/6		K40	91703-0006/9	93003-4240	A	YES					
93003-3514	91703-0005/8	93002-5004	NONE	2a	01c d50	2/3 4/5		K41	91703-0006/9	93003-4239	A	YES					
93003-3515	91703-0005/8	93002-5005	NONE	7b	01c d40 d70	1/2 3/4 6/7		K43	91703-0006/9	93003-4238	A	YES					
93003-3516	91703-0005/8	93002-5006	NONE	1b	03c d60	1/2 4/5		K31	91703-0006/9	93003-4237	A	YES					
93003-3517	91703-0005/8	93002-5007	NONE	1a 3a 4b 7b	01c d20 03c 06c	1/2 3/4 6/7		K45	91703-0006/9	93003-4236	A	YES					
93003-3518	91703-0005/8	93002-5008	NONE	1b 7a	02c d50	2/3 6/7		K48	91703-0006/9	93003-4235	A	YES					
93003-3519	91703-0005/8	93002-5009	NONE	1a 2b 3a 4b 6a	d20 03c d40 d50 d70	1/2 3/4 6/7		K51	91703-0006/9	93003-4234	A	YES					
93003-3520	91703-0005/8	93002-5010	NONE	1b 6a	d20 03c d50 d70	1/2 3/4 6/7		K69	91703-0006/9	93003-4233	A	YES					
93003-3505	91703-0005/8	93002-5011	NONE	1b 2a 5a 5b 7b	d20 d50 06c d70	1/2 4/5 6/7		K34	91703-0006/9	93003-4246	A	YES					
93003-3506	91703-0005/8	93002-5012	NONE	2b	d20 07c	1/2 3/4 5/6		K35	91703-0006/9	93003-4245	A	YES					
93003-3507	91703-0005/8	93002-5013	NONE	2a 2b 4b 5b 6a	d20 03c d40 d60	1/2 3/4 5/6		K38	91703-0006/9	93003-4244	A	YES					
93003-3510	91703-0005/8	93002-5014	NONE	2b 4a 4b 5b 6a	01c d20 d40 d60	1/2 3/4 5/6		K42	91703-0006/9	93003-4241	A	YES					
93003-3521	91703-0005/8	93002-5016	NONE	ALL	ALL	1/2 5/6		K00	91703-0006/9	93003-4232	A	YES					
93003-3522	91703-0005/8	93002-5019	CCT 6	ALL	03c d40 07c	1/2 5/6		---	91703-0006/9	93003-4231	A	YES					
93003-3523	91703-0005/8	93002-5000	NONE	NONE	03c d40 07c	1/2 5/6		K01	91703-0006/9	93003-4230	A	NO					
93003-3524	91703-0005/8	93002-5020	NONE	ALL	ALL	1/2 4/5 6/7		K101	91703-0006/9	93003-4229	A	YES					
93003-3525	91703-0005/8	93002-5019	NONE	ALL	03c d40 07c	1/2 5/6		---	91703-0006/9	93003-4228	A	YES					
93003-3526	91703-0005/8	93002-5017	CCT 4,5,6	2a 3b 4b 5a 6a 6b 7a	01c d30 04c 06c d60 d70	1/2 4/5		---	91703-0006/9	93003-4227	A	YES					
93003-3527	91703-0005/8	93002-5017	CCT 4	2a 3b 4b 5a 6a 6b 7a	01c d30 04c 06c d60 d70	1/2 4/5		---	91703-0006/9	93003-4226	A	YES					
93003-3529	91703-0005/8	93002-5024	NONE	3a 4b 7a	ALL	1/2 5/6		---	91703-0006/9	93003-4225	A	YES					

FUNCTIONAL SYMBOLS

= 0

= 0

= 0

DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

1:1

GENERAL TOLERANCES
(UNLESS SPECIFIED)

ANGULAR TOL ± 2.0 °

4 PLACES

±

3 PLACES

±

2 PLACES

± 0.1

1 PLACE

± 0.2

0 PLACES

±

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

SERIES

A1-SIZE

93003

CURRENT REV DESC:

EC NO: 749359

DRWN: RAHULH3

CHK'D: RAHULH3

APPR: MRAMAKRISHNA

INITIAL REVISION:

DRWN: AKABADI

APPR: BRUTTLE

2023/05/12

2023/05/12

2023/05/12

2017/09/08

2017/11/10

DOCUMENT NUMBER

DOC TYPE

DOC PART

REVISION

930030001

PSD

000

B1

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

SEE SHEET 3-11

GENERAL MARKET

10 OF 11

DOCUMENT STATUS	P1	RELEASE DATE	2023/05/12	09:50:23													
18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1

