

MMIC SURFACE MOUNT Directional Coupler

EDC10-273+

50Ω 10 dB 6 to 26.5 GHz

THE BIG DEAL

- · Wideband, 6-26.5 GHz
- Excellent Coupling Flatness 10 ± 1.5 dB Typ.
- Highly Repeatable Performance (GaAs Based Design)
- Small Size, 4x4 mm
- No External Termination Required



Generic photo used for illustration purposes only

CASE STYLE: DG1847

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our website for RoHS Compliance methodologies and qualifications

APPLICATIONS

- Satellite Communications
- Wireless Infrastructure
- Test and Measurements

PRODUCT OVERVIEW

Mini-Circuits' EDC10-273+ is a 10 dB directional coupler that operates from 6 to 26.5 GHz and is packaged in an MCLP 4x4 mm, 24-lead package. It provides excellent coupling flatness over a broad bandwidth and good return loss. This coupler also provides a quadrature phase shift between the signal at the through port and coupler port. Manufactured using GaAs Technology, this model is highly repeatable in volume manufacturing.

KEY FEATURES

| Feature | Advantages | | |
|---------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| Wideband, 6-26.5 GHz | EDC10-273+ can be used in many applications, saving component count. Also ideal for wideband applications such as military and instrumentation. | | |
| Excellent Coupling Flatness | Excellent coupling flatness yields higher accuracy. | | |
| Small Size, 4x4 mm MCLP Package | Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB. | | |

REV. A ECO-012570 EDC10-273+ MCL NY





Directional Coupler

EDC10-273+

ELECTRICAL SPECIFICATIONS¹ AT +25°C

| Parameter | Frequency (MHz) | Min. | Тур. | Max. | Unit | |
|-----------------------|-----------------|------|------|-------|------|--|
| Frequency Range | | 6000 | | 26500 | MHz | |
| Mainline Loss | 6000 - 10000 | | 1.0 | 2.2 | dB | |
| | 10000 - 18000 | | 1.4 | 2.3 | | |
| | 18000 - 23000 | | 1.5 | 3.2 | | |
| | 23000 - 26500 | | 1.8 | | | |
| Nominal Coupling | 6000 - 10000 | 9.2 | 10.3 | 12.5 | dB | |
| | 10000 - 18000 | 9.5 | 10.4 | 11.9 | | |
| | 18000 - 23000 | 9.8 | 11.4 | 13.3 | | |
| | 23000 - 26500 | 8.6 | 10.1 | 13.0 | | |
| Coupling Flatness (±) | 6000 - 26500 | | 1.5 | | dB | |
| Directivity | 6000 - 10000 | 10 | 16 | | dB | |
| | 10000 - 18000 | 8.9 | 15 | | | |
| | 18000 - 23000 | 8.5 | 14 | | | |
| | 23000 - 26500 | | 11 | | | |
| Return Loss (Input) | 6000 - 10000 | | 24 | | dB | |
| | 10000 - 18000 | | 17 | | | |
| | 18000 - 23000 | | 15 | | | |
| | 23000 - 26500 | | 15 | | | |
| Return Loss (Output) | 6000 - 10000 | | 22 | | | |
| | 10000 - 18000 | | 16 | | dB | |
| | 18000 - 23000 | | 16 | | | |
| | 23000 - 26500 | | 19 | | | |
| Return Loss (Coupled) | 6000 - 10000 | | 24 | | | |
| | 10000 - 18000 | | 16 | | | |
| | 18000 - 23000 | | 14 | | dB | |
| | 23000 - 26500 | | 14 | | | |

^{1.} Measured on Mini-Circuits Characterization test board TB-EDC10-273+ with testboard loss deducted.



Directional Coupler

EDC10-273+

ABSOLUTE MAXIMUM RATINGS


| Parameter | Ratings |
|-------------------------------|--------------------------------------------------|
| i didiletel | Ruthigs |
| Operating Temperature | -40°C to +85°C |
| Storage Temperature | -65°C to +150°C |
| Input Power | +28 dBm (5 minutes max.) +25 dBm (continuous) |
| Power at Internal Termination | +19 dBm (5 minutes max.) +16 dBm (continuous) |

Permanent damage may occur if any of these limits are exceeded.


PAD CONNECTIONS

| Function | Pad Number |
|------------------------|------------------|
| INPUT | 5 |
| COUPLED | 2 |
| OUTPUT | 14 |
| GROUND | Paddle |
| NC (GROUND EXTERNALLY) | 1,3,4,6-13,15-24 |

ELECTRICAL SCHEMATIC



PRODUCT MARKING



Marking may contain other features or characters for internal lot control.



Directional Coupler

EDC10-273+

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. TO ACCESS

CLICK HERE

| Performance Data | Data Table Swept Graphs S-Parameter (S3P Files) Data Set (.zip file) |
|------------------------------------------------------|----------------------------------------------------------------------------|
| Case Style | DG1847 Plastic package, exposed paddle Lead Finish: Matte-Tin |
| Tape & Reel Standard Quantities Available on Reel | F68 7" Reels with 20, 50, 100, 200, 500 or 1000 devices |
| Suggested Layout for PCB Design | PL-614 |
| Evaluation Board | TB-EDC10-273+ |
| Environmental Ratings | ENV08T2 |


ESD RATING

Human Body Model (HBM): Class 1B (Pass 500 V) in accordance with ANSI/ESD STM 5.1 - 2001

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020E /JEDEC J-STD-033C

MSL TEST FLOW CHART



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

