



Mini-Circuits®

CERAMIC

Low Pass Filter


50Ω

DC to 2200 MHz

LFCN-2250D+

FEATURES

- Excellent Power Handling, 10 W
- Small Size
- 7 Sections
- Temperature Stable
- LTCC Construction
- Protected by U.S Patent 6,943,646



Generic photo used for illustration purposes only

CASE STYLE: FV1206

APPLICATIONS

- Harmonic Rejection
- VHF/UHF Transmitters/Receivers
- Lab Use

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for RoHS Compliance methodologies and qualifications

ELECTRICAL SPECIFICATIONS^{1,2} AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	DC-F1	DC-2200		1.2	dB
	Freq. Cut-Off	F2	2575	3.0		dB
	VSWR	DC-F1	DC-2200	1.2		:1
Stopband	Rejection Loss	F3	2900	20		
		F4-F5	3000-5000	30		dB
		F6	7200	20		
		F3-F6	2900-7200	20		:1

¹. DC Resistance to ground is 100 Mohms min.². Measured on Mini-Circuits Characterization Test Board TB-LFCN-2250D+.


ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input ³	10 W max. at +25°C
Max. DC Voltage at Pins 1 & 3	+25 VDC
DC Current Input to Output	0.5 A max. at +25°C


³. Derate linearly to 3.5 W at +100°C ambient.

Permanent damage may occur if any of these limits are exceeded.

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC



REV. L
ECO-011331
LFCN-2250D+
MCL NY
250625

Mini-Circuits®



Mini-Circuits®

CERAMIC

Low Pass Filter

LFCN-2250D+


50Ω DC to 2200 MHz

PIN CONNECTIONS

RF IN	1
RF OUT	3
GROUND	2,4

PRODUCT MARKING: EK


DEMO BOARD MCL P/N: TB-LFCN-2250D+
SUGGESTED PCB LAYOUT (PL-137)




NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH THICKNESS .020" ± .0015".
COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH & GAP MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 -  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern



OUTLINE DIMENSIONS (Inches mm)

A	B	C	D	E	F	G	
.126	.063	.037	.020	.032	.009	.169	
3.20	1.60	0.94	0.51	0.81	0.23	4.29	
H	J	K	L	M	N	P	wt
.087	.024	.122	.024	.087	.012	.071	grams
2.21	0.61	3.10	0.61	2.21	0.30	1.80	.020

TAPE & REEL INFORMATION: F71



CERAMIC

Low Pass Filter



LFCN-2250D+

Mini-Circuits

50Ω DC to 2200 MHz

TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.02	1.03
500	0.16	1.04
1000	0.23	1.05
2200	0.79	1.33
2300	0.95	1.36
2400	1.19	1.36
2500	1.64	1.36
2550	2.09	1.44
2600	2.88	1.69
2650	4.39	2.26
2750	11.10	4.96
2850	23.25	8.77
2950	40.72	11.69
7000	30.04	24.48
8000	11.32	11.24



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

