





RUBBER PART GENERAL TOLERANCE


PART DIM.	1	②	3
0 TO 3	±0.2	±0.3	±0.4
3 TO 6	±0.2	±0.4	±0.5
6 TO 10	±0.3	±0.5	±0.6
10 TO 18	±0.3	±0.6	±0.8
18 TO 30	±0.4	±0.8	±1.0
30 TO 50	±0.5	±1.0	±1.5
50 TO 80	±0.6	±1.2	±2.0
80 TO 120	±0.7	±1.4	±2.5
120 TO 180	±0.8	±1.6	±3.0
180 TO 250	±1.0	±2.0	±4.0
250 TO 315	±1.2	±2.5	±5.0
315 TO 400	±1.5	±3.0	±6.0
400 TO 500	±1.8	±3.5	±7.0
500 OVER	±0.4%	±0.8%	±1.5%



ISOMETRIC VIEW



SECT AA



MATING HOLE SHAPE

相手穴形状 (t = 1.2 ~ 1.5)

注記

- 基本肉厚: t=1.5mm
- 適用パネル: $\phi 20$ 、t=1.2~1.5

NOTES

- GENERAL THICKNESS: t=1.5mm
- APPLICABLE PANEL: $\phi 20$, t=1.2~1.5

ISSUE MARK

								CUSTOMER					MATL. EPDM (BLACK)					TREAT. & FIN.					
								CUSTOMER PART NO.				CUSTOMER DWG NO.						SPEC.					
	05.12.02	NEW			C05-2144	N. H	OFFICE				TRIAL PART NO.						NAME						
LET	DATE	REVISION RECORD			NO.	CHKD	VENDER										GROMMET						
GENERAL TOLERANCE							VENDER NO.																
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE		DWG SOURCE		DWG DATE		UNIT	SCL	ANGLE	PART NO.						
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R		NEW		05.12.02		mm	1:1	3	7035-2835-30						
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED		CHECKED	CHECKED	DESIGN		DRAWN			CH. CODE						
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	T. SUGIYAMA		T. KATSUMATA				T. SHIMADA		N. HANADUMI		DWG NO.					
SPECIFIED							SEE RUBBER PART							MASS				7 g		7035-2835-30:R		SET DWG NO.	
							GENERAL TOLERANCE													YAZAKI CORPORATION			