


3

2

1

△	PART NO.	TREAT. & FIN.	APPLICABLE WIRE SIZE	W ₁	H ₁	W ₂	H ₂
	7114-2882						
	7114-2882-02	TIN PLATED	CAVUS 0.3~AV 0.5	2.7	2.5	3.8	3.5
	7114-2883						
	7114-2883-02	TIN PLATED	CAVUS 0.85~AV 2	3.7	3.4	5.5	4.8



										ISSUE MARK	
MATERIAL: Δ BRASS SPEC. (t=0.4)		TREAT. & FIN.		Δ SEE TABLE							
NAME M-US TYPE TERMINAL MALE											

PART NO.		7114-2882 ETC.									
CH. CODE											
DWG NO.		7114-2882:R									
SET DWG NO.											
YAZAKI CORPORATION											
CUSTOMER		CUSTOMER DWG NO.									
CUSTOMER PART NO.											
OFFICE		TRIAL PART NO.									
VENDOR											
VENDOR NO.											
DWG TYPE		DWG SOURCE		DWG DATE		UNIT		SCL		ANGLE	
R		NEW		1990/09/06		mm		2:1		3	
APPROVED		CHECKED		CHECKED		DESIGN		DRAWN			
M. KASHIYAMA		Y. FUKASE				K. JINNO		E. ITALIA			
2012/02/21		2012/02/21				1989/04/04		2012/02/21			
SPECIFIED		MASS									
10MAX 50MAX 100MAX 250MAX 2500VR		ANGLE		ECCENT							
A ± 0.15 ± 0.2 ± 0.3 ± 0.5 ± 0.75 $\pm 30'$		0.1									
B ± 0.2 ± 0.3 ± 0.55 ± 0.95 ± 1.4 $\pm 30'$		0.1									
C ± 0.3 ± 0.5 ± 0.8 ± 1.4 ± 2 $\pm 30'$		0.15									

3

2

1