





PART NUMBER	APPLICABLE WIRE SIZE		GRIP DIMENSIONS	
	CONDUCTOR (mm)	INSULATION (mm)	A	B
7114-3286-08	0.22 - 0.35	1.19 - 1.70	1.70	2.80
7114-3287-08	0.5 - 0.75	1.40 - 2.20	2.10	3.30



(1/1)



SECTION B-B



SECTION C-C



SECTION A-A

- NOTES:
1. PARTS MUST BE PURCHASED FROM YAZAKI.
 2. PARTS MUST BE FREE OF BURRS AND SHARP EDGES THAT MAY BE DETRIMENTAL TO SATISFACTORY ASSEMBLY, SAFE HANDLING, OR FUNCTION OF THE PART.
 3. MATING TERMINAL NUMBER: 7116-4720-08, ETC.
 4. MATERIAL: BRASS.
 5. PLATING TREATMENT: GOLD (Au) PLATING.
 6. PART DESIGNED TO SATISFY USCAR-2 REV. 3 DATED APRIL 2001 (CLASS 2).
 7. PART TO COMPLY WITH VPES-31-038 REQUIREMENTS.
 8. THIS DRAWING IS TO BE USED FOR INTERNAL YAZAKI PSW SUBMISSION.

ISSUE MARK

CUSTOMER		MAIL SPEC.		TREAT. & FIN.	
CUSTOMER PART NO.		CUSTOMER DWG NO.		NAME	
OFFICE		TRIAL PART NO.		YESC 0.64mm Au PLATED	
VENDOR		VENDOR NO.		MALE TERMINAL	
DWG TYPE		DWG SOURCE		DWG DATE	
R		7114-3286-08 M/A		12-09-2013	
APPROVED		CHECKED		DESIGN	
J. GAGNON		IVAN ZAPATA		04-19-2004	
PART NO.		CH. CODE		7114-3286-08 ETC.	
DWG NO.		7114-3286-08:R		YAZAKI CORPORATION	

GENERAL TOLERANCE											
10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5MAX	R10MAX	R20MAX	R200VR	ANGLE	ECCENT	WEIGHT
A ±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0.1	g
B ±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5	±3°	0.1	
C ±0.3	±0.5	±0.8	±1.4	±2	±0.2	±0.3	±0.5	±2.5	±3°	0.15	
SPECIFIED											

12-09-2013	NEW	C13-A677	I. Z.
DATE	REVISION RECORD	NO.	CHKD