







SEC. A-A

SEC. B-B



SEC. C-C

PART NO. AND CH. CODE	W1	H1	W2	H2	APPLICABLE WIRE SIZE
7114-5276-02	1.25	1.40	1.70	1.74	AWG 28 CABLE DIAMETER 0.85~0.95
7114-7333-02	1.82	2.19	2.45	2.68	ISO 0.35 mm ² ~0.50 mm ² CABLE DIAMETER 1.10~1.70
7114-4618-02	1.85	2.19	2.94	3.13	AWG 22~20 CABLE DIAMETER 1.50~1.90
7114-4619-02	1.96	2.52	2.94	3.13	ISO 0.75 mm ² CABLE DIAMETER 1.50-1.90

					CUSTOMER			MATL. SPEC.						BRASS (t=0.2)		TREAT. & FIN.		COPPER BASE/ TIN PLATING		
								CUSTOMER PART NO.			CUSTOMER DWG NO.						NAME KAIZEN 0.64 TERMINAL MALE			
△	06-24-2011	ADD PART NUMBER			C11-A563	E. Z.														
	07-09-2004	NEW			C04-Z687	Y. I.				TRIAL PART NO.										
LET	DATE	REVISION RECORD			NO.	CHKD	VENDOR													
GENERAL TOLERANCE								VENDOR NO.												
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.						
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	07-09-2004	mm	5/1	3	7114-4618-02 ETC.						
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	DWG NO.		7114-4618-02:R		SET DWG NO.			
Ⓒ	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15				Y. ITO		E. ZWART		YAZAKI CORPORATION					
SPECIFIED						MASS					06-14-2004		06-24-2011							
						g														