




1

2

3

RUBBER PART GENERAL TOLERANCE			
PART DIM.	1	2	③
0 TO 3	±0.2	±0.3	±0.4
3 TO 6	±0.2	±0.4	±0.5
6 TO 10	±0.3	±0.5	±0.6
10 TO 18	±0.3	±0.6	±0.8
18 TO 30	±0.4	±0.8	±1.0
30 TO 50	±0.5	±1.0	±1.5
50 TO 80	±0.6	±1.2	±2.0
80 TO 120	±0.7	±1.4	±2.5
120 TO 180	±0.8	±1.6	±3.0
180 TO 250	±1.0	±2.0	±4.0
250 TO 315	±1.2	±2.5	±5.0
315 TO 400	±1.5	±3.0	±6.0
400 TO 500	±1.8	±3.5	±7.0
500 OVER	±0.4%	±0.8%	±1.5%



ISOMETRIC VIEW

- NOTES:
- PARTS MUST BE PURCHASED FROM YAZAKI.
 - PART MUST BE FREE OF BURRS AND FLASH THAT AFFECT THE FUNCTION OF THE PART.
 - MATERIAL: SELF-LUBRICATING SILICONE RUBBER.
COLOR: SEE TABLE.
 - APPLICABLE WIRE: SEE TABLE.
 - APPLICABLE WIRE SHIELD TERMINAL: 7185-0499-02 OR EQUIVALENT
 - PART TO COMPLY WITH YPES-31-038.
 - THIS DRAWING IS TO BE USED FOR INTERNAL YAZAKI PSW SUBMISSION.

					CUSTOMER										MATL. SPEC.		SEE NOTES		TREAT. & FIN.		SEE NOTES					
								CUSTOMER PART NO.					CUSTOMER DWG NO.													
																		NAME								
-	03/14/2019	NEW				C19-A260			M.H.		OFFICE YNA					TRIAL PART NO.					2P 8mm SP SEALED 90° MALE CONNECTOR ----- WIRE SEAL					
LET	DATE	REVISION RECORD				NO.			CHKD		VENDOR					X31658-A094; X31658-A736										
GENERAL TOLERANCE										VENDOR NO.																
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE		DWG DATE	UNIT	SCL	ANGLE	PART NO. 7172-5653-90, ETC.											
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	7172-5653-90:M/A		03/14/2019	mm	2:1	3	CH. CODE											
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		DWG NO. 7172-5653-90:R						SET DWG NO.						
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15				K. PAKRAVAN	M. HOLTHUS														
SPECIFIED							MASS							05/5/2017		03/14/2019		YAZAKI CORPORATION								
							SEE TABLE																			

1

2

3