


1

2

3

SUB ASS'Y NO.	NO.	PART NO.	MATERIAL	COLOR	QTY.
7282-5536-40	①	7182-5536-40	HPA	LIGHT GRAY	1
	②	7158-4159	HPA	NATURAL	1





注記

1. 嵌合相手品番 : 7283-5536-40
2. 適用ターミナル品番 : 7114-4100-02 ETC.

NOTES

1. MATING PART NO. : 7283-5536-40
2. APPLICABLE TERMINAL PART NO. : 7114-4100-02 ETC.



ISSUE MARK

CUSTOMER										MATL. SPEC.				TREAT. & FIN.			
CUSTOMER PART NO.										CUSTOMER DWG NO.				SEE TABLE			
98.01.30 NEW. A C97-M910 H. K										OFFICE				NAME 1.5 SYSTEM CONNECTOR			
LET DATE REVISION RECORD NO. CHKD										VENDOR				TRIAL PART NO.			
GENERAL TOLERANCE										VENDOR NO.				16P (M) SUB ASS'Y (TYPE-C)			
	10MAX	50MAX	100MAX	250MAX	250QVR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.	7282-5536-40. A		
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	97.10.20	mm	2/1	3	CH. CODE			
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		DWG NO.	7282-5536-40:R		
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	遠藤	斎藤	大島	K. OHTAKA	ITOH		SET DWG NO.			
SPECIFIED								MASS		98.02.11.		98.2.11		98.02.11		95.06.30 98.01.30	
								g		98.02.11.		98.2.11		98.02.11		95.06.30 98.01.30	
YAZAKI CORPORATION																	

1

2

3