




1

2

3



SUB ASS'Y PART NO.	NO.	PART NO.	MATERIAL & COLOR
7283-4260	①	7183-4260	PBT (NATURAL)
	②	7157-4613-80	PBT (BROWN)
7283-4260-30	①	7183-4260-30	PBT (BLACK)
	②	7157-4613-80	PBT (BROWN)

注記

1. 適用端子番 : 187 7116-4045-02 ETC.
SDL 7116-1473 ETC.

NOTE

1. APPLICABLE TERMINAL PART NO. : 187 7116-4045-02 ETC.
SDL 7116-1473 ETC.

ISSUE MARK

										CUSTOMER				MATL. SPEC.				SEE TABLE				TREAT. & FIN.				ISSUE MARK					
										CUSTOMER PART NO.				CUSTOMER DWG NO.																	
△ 00.08.21 ADDED COLOUR CODE C00-P175 M. P.																		NAME HYBRID CONNECTOR FEMALE 6P SUB-ASS'Y (REAR HOLDER TYPE)													
94.06.01 NEW C94-L527 H. F										OFFICE				TRIAL PART NO.																	
LET DATE REVISION RECORD NO. CHKD										VENDOR				-----																	
										VENDOR NO.				-----																	
GENERAL TOLERANCE																															
10MAX 50MAX 100MAX 250MAX 2500VR ANGLE ECCENT										DWG TYPE		DWG SOURCE		DWG DATE		UNIT		SCL		ANGLE		PART NO.									
A ±0.15 ±0.2 ±0.3 ±0.5 ±0.75 ±30' 0.1										R		NEW		00.08.21		mm		2/1 3		7283-4260 ETC △											
B ±0.2 ±0.3 ±0.55 ±0.95 ±1.4 ±30' 0.1										APPROVED		CHECKED		CHECKED		DESIGN		DRAWN		DWG NO.											
© ±0.3 ±0.5 ±0.8 ±1.4 ±2 ±30' 0.15										Clayton				Clayton		K. SAKURAI		PEREZ		7283-4260:R											
SPECIFIED										MASS		g		00.8-23		00.8-23		91.04.19		00.08.21		YAZAKI CORPORATION									