







3

GENERAL TOLERANCE											
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0
B	±0.2	±0.3	±0.55	±0.95	±1.4					±3°	0.1
Ⓒ	±0.3	±0.5	±0.8	±1.4	±2.0					±3°	0.15
SPECIFIED										MASS	SEE TABLE

CUSTOMER							MATL. SPEC.		SEE TABLE		TREAT. & FIN.		N/A	
CUSTOMER PART NO.				CUSTOMER DWG NO.			NAME							
OFFICE YNA				TRIAL PART NO.			Y-TYPE (9.5mm SEALED) CONNECTOR							
VENDOR				X40183-A512, X40283-A556			2P (F) SUB ASSY							
VENDOR NO.							PART NO. 7283-3214-30, ETC.							
DWG TYPE		DWG SOURCE		DWG DATE		UNIT	SCL	ANGLE	DWG NO. 7283-3214-30:R					
R		7283-3214-30-M		11-17-2003		mm	2/1	3						
APPROVED		CHECKED		CHECKED		DESIGN		DRAWN		DWG NO. 7283-3214-30:R				
						H. ALI		DAVID ZYBACH						
						11-20-2002		10-28-2016		YAZAKI CORPORATION				