

1

2

3

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	QTY.
7283-7476	①	7183-7476	PBT	NATURAL	1
	②	7158-4639	PBT	NATURAL	1

注 記

1. 適用端子品番 : 1. 0Ⅲ (040Ⅲ) 7116-4233-08 ETC.

2. 3Ⅱ (090Ⅱ) 7116-4020 ETC.

2. 取り付可能部品 : 7283-6038, -6039, 7C83-6038

7158-7173-30, -7174-30


NOTES

1. APPLICABLE TERMINAL NO. : 1. 0Ⅲ (040Ⅲ) 7116-4233-08 ETC.



2. 3Ⅱ (090Ⅱ) 7116-4020 ETC.

2. APPLICABLE PART NO. : 7283-6038, -6039, 7C83-6038

7158-7173-30, -7174-30



A ←



SEC. A-A

ISSUE MARK

CUSTOMER					MATL. SPEC. SEE TABLE					TREAT. & FIN.				
CUSTOMER PART NO.					CUSTOMER DWG NO.									
01.11.28 NEW C01-Y252 T.Y					OFFICE TRIAL PART NO.					NAME 1. 0Ⅲ (040Ⅲ) 12P + 2. 3Ⅱ (090Ⅱ) 4P HYBRID LIF				
LET DATE REVISION RECORD NO. CHKD					VENDOR					CONNECTOR C-HOUSING FEMALE SUB ASSEMBLY				
GENERAL TOLERANCE					VENDOR NO.									
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	01.11.28	mm	2/1	3	7283-7476
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		CH. CODE
©	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15				YAMASHITA	OHKUBO		7283-7476:R
SPECIFIED					MASS									SET DWG NO.
					g									YAZAKI CORPORATION

1

2

3