

# ME 35 UTMG BK - Mounting base housing



2910004

<https://www.phoenixcontact.com/us/products/2910004>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Intermediate element, Lower housing part, tall design, without vents, width: 17.6 mm, height: 99 mm, depth: 74 mm, cross connection: without bus connector, number of positions cross connector: not relevant

## Your advantages

- Can be mounted on the DIN rail
- With integrated or DIN-rail-mountable bus connector as an option

## Commercial data

Item number	2910004
Packing unit	100 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHAAZ
GTIN	4017918420109
Weight per piece (including packing)	22.2 g
Weight per piece (excluding packing)	17.6 g
Country of origin	DE

# ME 35 UTMG BK - Mounting base housing



2910004

<https://www.phoenixcontact.com/us/products/2910004>

## Technical data

### Product properties

Product type	Component housing center part
Housing type	Intermediate element
Product family	ME UTM
Number of positions	999
Type	Lower housing part, tall design
Ventilation openings present	no

### Dimensions

Width	17.6 mm
Height	99 mm
Depth	74 mm
Depth from top edge of DIN rail	68.5 mm
Depth from top edge of DIN rail to support point on upper part	68.5 mm

### Material specifications

Color	black (9005)
Flammability rating according to UL 94	V0
Housing material	PA

### Environmental and real-life conditions

#### Power dissipation single housing for 20 °C

Ambient temperature	20 °C
Reduction factor	1
Mounting position	vertical
Power dissipation	7.5 W

#### Power dissipation single housing for 30 °C

Ambient temperature	30 °C
Reduction factor	0.91
Mounting position	vertical
Power dissipation	6.8 W

#### Power dissipation single housing for 40 °C

Ambient temperature	40 °C
Reduction factor	0.81
Mounting position	vertical
Power dissipation	6.1 W

#### Power dissipation single housing for 50 °C

Ambient temperature	50 °C
Reduction factor	0.7

# ME 35 UTMG BK - Mounting base housing



2910004

<https://www.phoenixcontact.com/us/products/2910004>

Mounting position	vertical
Power dissipation	5.2 W

## Power dissipation single housing for 60 °C

Ambient temperature	60 °C
Reduction factor	0.57
Mounting position	vertical
Power dissipation	4.3 W

## Power dissipation single housing for 70 °C

Ambient temperature	70 °C
Reduction factor	0.49
Mounting position	vertical
Power dissipation	3.7 W

## Ambient conditions

Max. IP code to attain	IP20
------------------------	------

## PCB data

Type of PCB mount	Latching
-------------------	----------

## Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

# ME 35 UTMG BK - Mounting base housing



2910004  
<https://www.phoenixcontact.com/us/products/2910004>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)