

V _{DS}	1200 V
$R_{DS,on}$	77 mΩ
I _{D (TC=25C)}	35 A
T _i ,max	175°C

QSiC™ 1200V SiC MOSFET

Features

- High speed switching
- Reliable body diode
- All parts tested to greater than 1,400V
- Avalanche tested to 200mJ
- Driver source pin for gate driving


Benefits

- Lower capacitance
- Higher system efficiency
- Easy to parallel
- Lower Switching Loss
- · Longer clearance distance

Applications

- Solar Inverters
- Switch mode power supplies, UPS
- · Induction heating and welding
- EV charging stations
- High voltage DC/DC converters
- · Motor drives

Package



(Tab) D (Drain) (1) G (Gate) (2) S_G (Driver Source) (3-7) S (Source)

Part #	Package	Marking
GP2T080A120J	TO-263-7L	2T080A120J



Maximum Ratings, at T_j =25°C, unless otherwise specified

Characteristics	Symbol	Conditions	Values	Unit
Drain-Source Voltage	V _{rated}	V _{GS} =0V, I _{DS} =1µA	1200	V
Continuous Drain Current	ı	T _C =25 °C, T _j =175 °C	35	
Continuous Diain Current	l _D	T _C =100 °C, T _j =175 °C	26	Α
Pulsed Drain Current	I _{D,pulse} *	T _C =25°C	80	
Gate Source Voltage	V_{GSmax}		-10/25	V
Gate Source voltage	V_{GSop}	Recommended operational	-5/20]
Power Dissipation	P _{tot}	T _C =25°C	188	W
Operating & Storage Temperature	T _{j,} T _{storage}	Continuous	-55175	°C
Single Pulse Avalanche Energy	E _{AS}	L=1.0mH, I _{AS} =20.0A, V=50V	200	mJ

Thermal Characteristics

Characteristics	Symbol Conditions	Conditions	Values			Unit
Citatacteristics	Syllibol	Conditions	min.	typ.	max.	Oilit
Thermal Resistance, Junction to Case	R _{thJC}		-	0.61	0.80	
Thermal Resistance, Junction to Ambient	R _{thJA}		-	-	40.0	°C/W

^{*} Pulse width is limited by Tj_{max}

Static Electrical Characteristics, at T_j =25°C, unless otherwise specified

Characteristics	Symbol	Conditions	Values			Unit
Characteristics	Symbol		min.	typ.	max.	Onit
Drain-Source Breakdown Voltage	BV _{DSS}	I _{DS} =1mA	1200	-	-	V
Zero Gate Voltage Drain Current	1	V _{DS} =1200V, V _{GS} =0V	-	0.1	1.0	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =1200V, V _{GS} =0V, T _j =175°C	-	1	-	μA
Cata Sauraa Laakaga Current	I _{GSS+}	V _{GS} =20V, V _{DS} =0V	-	10	100	ъ^
Gate-Source Leakage Current	I _{GSS-}	V _{GS} =-5V, V _{DS} =0V	-	-10	-100	nA
	V _{GS(th)}	V _{GS} =V _{DS} , I _{DS} =10mA	1.8	2.8	4	V
Gate Threshold Voltage		V _{GS} =V _{DS} , I _{DS} =10mA, T _j =125°C	-	2.1	-	
		$V_{GS}=V_{DS}$, $I_{DS}=10$ mA, $T_j=175$ °C	-	1.9	-	
Drain-Source On-Resistance	R_{DSon}	V _{GS} =20V, I _{DS} =20A	-	77	100	
		V _{GS} =20V, I _{DS} =10A	-	71	90	- mΩ
		V _{GS} =20V, I _{DS} =20A, T _j =125°C	-	106	-	
		V _{GS} =20V, I _{DS} =20A, T _j =175°C	-	134	-	
Transconductance	9 _{fs}	V _{DS} =20V, I _{DS} =20A	-	8	-	S
Gate Input Resistance	R _G	f=1MHz, V _{AC} =25mV, D-S Short		3.0		Ω


AC Electrical Characteristics, at $T_j \!\!=\!\! 25^{\circ}\text{C},$ unless otherwise specified

Characteristics	Cumbal	Conditions	Values			Unit
Citatacteristics	Symbol	Conditions	min.	typ.	max.	Ullit
Input Capacitance	C _{ISS}	\/ -0\/	-	1377	-	
Output Capacitance	Coss	V _{GS} =0V, V _{DS} =1000V,	-	62	-	pF
Reverse Transfer Capacitance	C _{RSS}	f=200kHz, V _{AC} =25mV	-	4	-	
Coss Stored Energy	Eoss	7 200KHZ, V _{AC} 20HV	-	38	-	μJ
Turn-On Switching Energy	E _{ON}	V _{DD} =800V, I _{DS} =20A,	-	208	-	
Turn-Off Switching Energy	E _{OFF}	$R_{G(ext)}$ =4.3, V_{GS} =-5/+20V, L=975 μ H, FWD=GP2T080A120J	-	29	-	μJ
Total Switching Energy	E _{TOT}		-	237	-	
Turn-On Delay Time	t _{D(on)}	V _{DD} =800V, I _{DS} =20A,	-	10	-	
Rise Time	t _R	R _{G(ext)} =4.3, V _{GS} =-5/+20V,	-	3	-	7
Turn-Off Delay Time	t _{D(off)}	L=975μH,	-	17	-	ns
Fall Time	t _F	FWD=GP2T080A120J	-	10	-	
Total Gate Charge	Q_G	V _{DD} =800V, I _{DS} =20A, V _{GS} =-5/+20V	-	53	-	
Gate to Source Charge	Q _{GS}		-	20	-	nC
Gate to Drain Charge	Q_{GD}	1 V GS 0/ 1 20 V	-	13	-	

Body Diode Characteristics, at Tj=25°C, unless otherwise specified

Characteristics	Symbol	Conditions		Values		Unit
Characteristics	Syllibol	Conditions	min.	typ.	max.	Onit
Max Continuous Diode Fwd Current	I _S	V _{GS} =-5V, T _C =25°C	-	-	43	Α
Diode Forward Voltage	V _{SD}	V _{GS} =-5V, I _{SD} =10A	-	3.8	-	V
Reverse Recovery Time	t _{RR}	-20A \/ -800\/ \/ - 5\/	-	8	-	ns
Reverse Recovery Charge	Q_{RR}	I _{SD} =20A, V _R =800V, V _{GS} =-5V, di _F /dt=8.65A/ns	-	158	-	nC
Peak Reverse Recovery Current	I _{RRM}	Tale 0.007 VII3	-	36	-	Α

Typical Performance







Figure 1. Output Characteristics T_i = -55°C











Figure 4. Output Characteristics $T_j = 175$ °C



300.0

250.0

Conditions:
V_{cs} = 20V
t_p = 100 µs

Tj=175°C

Tj=125°C

Tj=25°C

Tj=25°C

Tj=25°C


Tj=25°C

Tj=25°C

Tj=25°C

Figure 5. Normalized On-Resistance vs. Temperature

Figure 6. On-Resistance vs. Drain Current For Various Temperature







Figure 7. On-Resistance vs. Temperature For Various Gate Voltages

Figure 8. Transfer Characteristic for Various Junction Temperatures

QSiC™ 1200V SiC MOSFET

GP2T080A120J








Figure 9. Body Diode Characteristics at T_i = -55°C

Figure 10. Body Diode Characteristics at T_i = 25°C









Figure 12. Threshold Voltage vs. Temperature









Figure 13. Gate Charge Characteristics










Figure 16. Continuous Drain Current Derating vs.

Case Temperature




Figure 17. Maximum Power Dissipation Derating vs Case Temperature




Figure 19. Safe Operating Area




Figure 18. Transient Thermal impedance (Junction to Case)




Figure 20. Clamped Inductive Switching Energy vs.

Drain Current




Figure 21. Clamped Inductive Switching Energy vs. $R_{\text{G(ext)}} \label{eq:RG(ext)}$




Figure 23. Switching Times vs $R_{\text{G(ext)}}$




Figure 22. Clamped Inductive Switching Energy vs.
Temperature





Figure 24. Turn-off Transient Definitions









Figure 25. Turn-on Transient Definitions

Figure 26. Reverse Recovery Definitions

Package Dimensions TO-263-7L







Sym	Millin	neters	Inches		
Jyiii	Min	Max	Min	Max	
Α	4.30	4.57	0.169	0.180	
A1	0.00	0.25	0.000	0.010	
b	0.50	0.70	0.020	0.028	
С	0.33	0.65	0.013	0.026	
C2	1.17	1.40	0.046	0.055	
D	9.03	9.13	0.355	0.359	
D1	4.66	4.81	0.183	0.189	
D2	4.255	4.255 BSC		BSC	
D3	7.170) BSC	0.282 BSC		
Е	10.13	10.23	0.399	0.403	
E1	6.50	8.60	0.256	0.339	
E2	6.78	7.67	0.267	0.302	
е	1.22	1.32	0.048	0.052	
Н	15.04	17.12	0.592	0.674	
L3	0.254	BSC	0.010 BSC		

Notes

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented March, 2013. RoHS Declarations for this product can be obtained from the Product Documentation sections of www.SemiQ.com.

REACh Compliance

REACh substances of high concern (SVHC) information is available for this product. Since the European Chemicals Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact our office at SemiQ Headquarters in Lake Forest, California to insure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

SemiQ Inc., reserves the right to make changes to the product specifications and data in this document without notice. SemiQ products are sold pursuant to SemiQ's terms and conditions of sale in place at the time of order acknowledgement.

This product has not been designed or tested for use in, and is not intended for use in, applications implanted into the human body nor in applications in which failure of the product could lead to death, personal injury or property damage, including but not limited to equipment used in the operation of nuclear facilities, life-support machines, cardiac defibrillators or similar emergency medical equipment, aircraft navigation or communication or control systems, or air traffic control.

SemiQ makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SemiQ assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using SemiQ products.

To obtain additional technical information or to place an order for this product, please contact us. The information in this datasheet is provided by SemiQ. SemiQ reserves the right to make changes, corrections, modifications, and improvements of datasheet without notice.