

Han 1Mod AK-QB-Dichtung



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 5402
Specification	Han 1Mod AK-QB-Dichtung
HARTING eCatalogue	https://harting.com/09140015402

Identification

Category	Accessories
Series of hoods/housings	Han-Modular® Compact
Type of accessory	Protection cover
Description of the accessory	for carrier hoods Thermoplastic

Version

Size	Modular Compact
Locking type	Single locking lever
Details	Rated voltage ≤630 V Rated impulse voltage ≤6 kV Pollution degree 3 For a complete connector the specified voltage rating is the maximum level which can be achieved. In cases where the used module(s) do offer lower voltage ratings, then these lower ratings are valid. Higher voltage ratings in individual applications can be approved in coordination with HARTING.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 locked condition

Material properties

Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984
----------------	-----------

Commercial data

Packaging size	10
Net weight	20.16 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019522
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467