

# LPT 6/ 7-7,5-ZB - PCB terminal block



1098172

<https://www.phoenixcontact.com/us/products/1098172>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Printed circuit board terminal, nominal current: 41 A, rated voltage (III/2): 1000 V, nominal cross section: 6 mm<sup>2</sup>, number of potentials: 7, number of rows: 1, number of positions per row: 7, product range: LPT 6/, pitch: 7.5 mm, connection method: Lever Push-in connection, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: green, Pin layout: Zigzag pinning W, Solder pin [P]: 3.6 mm, type of packaging: packed in cardboard

## Your advantages

- Tool-free lever principle enables time-saving connection and release of conductors with/without ferrules
- Clear lever positions provide reliable feedback on opened or closed clamping spaces
- Defined contact force ensures that contact remains stable over the long term
- Time-saving push-in connection when lever is closed
- Intuitive operation, thanks to a color-coded actuation lever

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1098172                        |
| Packing unit                         | 25 pc                          |
| Minimum order quantity               | 50 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA14                           |
| Product key                          | AANTBA                         |
| GTIN                                 | 4055626941745                  |
| Weight per piece (including packing) | 34.58 g                        |
| Weight per piece (excluding packing) | 2.22 g                         |
| Customs tariff number                | 85369010                       |
| Country of origin                    | SK                             |

# LPT 6/ 7-7,5-ZB - PCB terminal block



1098172

<https://www.phoenixcontact.com/us/products/1098172>

## Technical data

### Product properties

|                       |                                |
|-----------------------|--------------------------------|
| Product type          | Printed circuit board terminal |
| Product family        | LPT 6/                         |
| Product line          | COMBICON Terminals L           |
| Number of positions   | 7                              |
| Pitch                 | 7.5 mm                         |
| Number of connections | 7                              |
| Number of rows        | 1                              |
| Number of potentials  | 7                              |
| Pin layout            | Zigzag pinning W               |

### Electrical properties

#### Properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 41 A   |
| Nominal voltage $U_N$       | 1000 V |
| Rated voltage (III/3)       | 1000 V |
| Rated surge voltage (III/3) | 8 kV   |
| Rated voltage (III/2)       | 1000 V |
| Rated surge voltage (III/2) | 8 kV   |
| Rated voltage (II/2)        | 1000 V |
| Rated surge voltage (II/2)  | 6 kV   |

### Connection data

#### Connection technology

|                       |                   |
|-----------------------|-------------------|
| Nominal cross section | 6 mm <sup>2</sup> |
|-----------------------|-------------------|

#### Conductor connection

|                                                                                           |                                                                                            |
|-------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Connection method                                                                         | Lever Push-in connection                                                                   |
| Conductor cross-section rigid                                                             | 0.2 mm <sup>2</sup> ... 10 mm <sup>2</sup> (Conductor connection with open terminal point) |
|                                                                                           | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup> (Push-in connection)                            |
| Conductor cross-section flexible                                                          | 0.34 mm <sup>2</sup> ... 10 mm <sup>2</sup>                                                |
| Conductor cross-section AWG                                                               | 22 ... 8                                                                                   |
| Conductor cross-section flexible, with ferrule without plastic sleeve                     | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup> (Conductor connection with open terminal point)  |
|                                                                                           | 1.5 mm <sup>2</sup> ... 6 mm <sup>2</sup> (Push-in connection)                             |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve                      | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup> (Conductor connection with open terminal point)  |
|                                                                                           | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup> (Push-in connection)                             |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                                |
| Stripping length                                                                          | 12 mm ... 14 mm                                                                            |

# LPT 6/ 7-7,5-ZB - PCB terminal block



1098172

<https://www.phoenixcontact.com/us/products/1098172>

## Mounting

|               |                  |
|---------------|------------------|
| Mounting type | Wave soldering   |
| Pin layout    | Zigzag pinning W |

## Material specifications

### Material data - contact

|                                          |                                                                                  |
|------------------------------------------|----------------------------------------------------------------------------------|
| Note                                     | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                         | Cu alloy                                                                         |
| Surface characteristics                  | Tin-plated                                                                       |
| Metal surface terminal point (top layer) | Tin (10 - 16 µm Sn)                                                              |
| Metal surface soldering area (top layer) | Tin (10 - 16 µm Sn)                                                              |

### Material data - housing

|                                                                   |              |
|-------------------------------------------------------------------|--------------|
| Color (Housing)                                                   | green (6021) |
| Insulating material                                               | PA           |
| Insulating material group                                         | I            |
| CTI according to IEC 60112                                        | 600          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

### Material data – actuating element

|                                        |               |
|----------------------------------------|---------------|
| Color (Actuating element)              | orange (2003) |
| Insulating material                    | PA GF         |
| Insulating material group              | I             |
| CTI according to IEC 60112             | 600           |
| Flammability rating according to UL 94 | V0            |

## Dimensions

|                       |          |
|-----------------------|----------|
| Dimensional drawing   |          |
| Pitch                 | 7.5 mm   |
| Width [w]             | 53.5 mm  |
| Height [h]            | 27.85 mm |
| Length [l]            | 24.3 mm  |
| Installed height      | 24.25 mm |
| Solder pin length [P] | 3.6 mm   |

# LPT 6/ 7-7,5-ZB - PCB terminal block



1098172

<https://www.phoenixcontact.com/us/products/1098172>

|                |              |
|----------------|--------------|
| Pin dimensions | 1.5 x 1.2 mm |
| PCB design     |              |
| Hole diameter  | 2 mm         |

## Mechanical tests

### Test for conductor damage and slackening

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
| Result        | Test passed         |

### Pull-out test

|                                                                             |                                          |
|-----------------------------------------------------------------------------|------------------------------------------|
| Specification                                                               | IEC 60999-1:1999-11                      |
| Conductor cross-section/conductor type/tractive force setpoint/actual value | 0.2 mm <sup>2</sup> / solid / > 10 N     |
|                                                                             | 0.34 mm <sup>2</sup> / flexible / > 15 N |
|                                                                             | 10 mm <sup>2</sup> / solid / > 90 N      |
|                                                                             | 10 mm <sup>2</sup> / flexible / > 90 N   |

## Electrical tests

### Temperature-rise test

|                                   |                                                                                                                                |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| Specification                     | IEC 60947-7-4:2019-01                                                                                                          |
| Requirement temperature-rise test | The sum of ambient temperature and temperature rise of the PCB terminal block shall not exceed the upper limiting temperature. |

### Short-time withstand current

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60947-7-4:2019-01 |
|---------------|-----------------------|

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | > 5 MΩ                |

### Air clearances and creepage distances |

|                                                        |                       |
|--------------------------------------------------------|-----------------------|
| Specification                                          | IEC 60947-7-4:2019-01 |
| Insulating material group                              | I                     |
| Comparative tracking index (IEC 60112)                 | CTI 600               |
| Rated insulation voltage (III/3)                       | 1000 V                |
| Rated surge voltage (III/3)                            | 8 kV                  |
| minimum clearance value - non-homogenous field (III/3) | 8 mm                  |
| minimum creepage distance (III/3)                      | 12.5 mm               |
| Rated insulation voltage (III/2)                       | 1000 V                |
| Rated surge voltage (III/2)                            | 8 kV                  |
| minimum clearance value - non-homogenous field (III/2) | 8 mm                  |
| minimum creepage distance (III/2)                      | 8 mm                  |
| Rated insulation voltage (II/2)                        | 1000 V                |
| Rated surge voltage (II/2)                             | 6 kV                  |
| minimum clearance value - non-homogenous field (II/2)  | 5.5 mm                |

# LPT 6/ 7-7,5-ZB - PCB terminal block



1098172

<https://www.phoenixcontact.com/us/products/1098172>

|                                  |        |
|----------------------------------|--------|
| minimum creepage distance (II/2) | 5.5 mm |
|----------------------------------|--------|

## Environmental and real-life conditions

### Vibration test

|                        |                                          |
|------------------------|------------------------------------------|
| Specification          | IEC 60068-2-6:2007-12                    |
| Frequency              | 10 - 150 - 10 Hz                         |
| Sweep speed            | 1 octave/min                             |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz)              |
| Acceleration           | 50 m/s <sup>2</sup> (60.1 Hz ... 150 Hz) |
| Test duration per axis | 2.5 h                                    |
| Test directions        | X-, Y- and Z-axis                        |

### Glow-wire test

|                  |                        |
|------------------|------------------------|
| Specification    | IEC 60695-2-10:2013-04 |
| Temperature      | 850 °C                 |
| Time of exposure | 5 s                    |

### Aging

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60947-7-4:2019-01 |
|---------------|-----------------------|

### Ambient conditions


|                                         |                                                                               |
|-----------------------------------------|-------------------------------------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 105 °C (Depending on the current carrying capacity/derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                                              |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                                                 |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                                              |

## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|


## Drawings

Diagram



Type: LPT 6/...-7,5-ZB

Diagram



Type: LPT 6/...-7,5-ZB

# LPT 6/ 7-7,5-ZB - PCB terminal block



1098172

<https://www.phoenixcontact.com/us/products/1098172>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1098172>

|  <b>UL Recognized</b><br>Approval ID: E60425-20210507 |                                |                                |                   |                               |
|----------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                                        | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| F                                                                                                                                      |                                |                                |                   |                               |
|                                                                                                                                        | 1000 V                         | 40 A                           | 22 - 8            | -                             |

|  <b>cULus Recognized</b><br>Approval ID: E60425-20210507 |                                |                                |                   |                               |
|-------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                                           | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| B                                                                                                                                         |                                |                                |                   |                               |
|                                                                                                                                           | 600 V                          | 40 A                           | 22 - 8            | -                             |
| C                                                                                                                                         |                                |                                |                   |                               |
|                                                                                                                                           | 600 V                          | 40 A                           | 22 - 8            | -                             |

|  <b>VDE approval of drawings</b><br>Approval ID: 40054188 |                                |                                |                   |                               |
|----------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                                              | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                        |                                |                                |                   |                               |
|                                                                                                                                              | 1000 V                         | 41 A                           | -                 | 0.2 - 6                       |

# LPT 6/ 7-7,5-ZB - PCB terminal block



1098172

<https://www.phoenixcontact.com/us/products/1098172>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460101 |
| ECLASS-15.0 | 27460101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002643 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# LPT 6/ 7-7,5-ZB - PCB terminal block



1098172

<https://www.phoenixcontact.com/us/products/1098172>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 1.021 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)