

FOC-SJ:14-SJ:14-HB02/3,5PR L04 - FO patch cable



1171602

<https://www.phoenixcontact.com/us/products/1171602>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled FO cable, PROFINET cable type B, 200/230 µm PCF fiber, SC-RJ/IP67 push-pull metal housing to BFOC(ST)/IP20, PVC outer sheath, halogen-free, ozone- and UV-resistant, in conduit, for fixed indoor installation, length: 3.5 m



Your advantages

- High degree of reliability, thanks to the exceptional quality
- Reliable even in EMC-sensitive applications
- Fast data transmission for demanding applications
- Flexible installation, thanks to PVC outer sheath
- Including individual test report
- Universal installation cables for fixed installation indoors and outdoors (direct underground installation not permitted)
- Additional line protection thanks to protective tube
- PROFINET type B for flexible use
- Robust cable for use in harsh environments

Commercial data

Item number	1171602
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOBS
GTIN	4063151196639
Weight per piece (including packing)	503 g
Weight per piece (excluding packing)	496.341 g
Customs tariff number	85447000
Country of origin	DE

Technical data

Product properties

Product type	Data cable preassembled
Application	Standard
Sensor type	Ethernet
Number of positions	2

Electrical properties

Transmission medium	PCF fiber
Transmission speed	100 Mbps
Transmission speed	100 Mbps

Dimensions

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Connector

Connection 1

Type	Plug straight Push-pull version 14
Degree of protection	IP65/IP67 (Push-Pull ADVANCE)

Connection 2

Type	Plug straight Push-pull version 14
Material	Zinc die-cast (nickel-plated)
Degree of protection	IP65/IP67

Cable/line

Cable length	3.50 m
Cable weight	45 kg/km
External cable diameter	8.00 mm ±0.5 mm
Outer sheath, material	TPE-U
External sheath, color	orange
Thickness, outer sheath	1 mm
Conductor structure signal line	500.00 µm ±30 µm
Thickness, insulation	approx. 0.60 mm
Wire diameter incl. insulation	2.9 mm ±0.1 mm
Single wire, color	red, green
Smallest bending radius, fixed installation	65 mm
Smallest bending radius, movable installation	65 mm
Halogen-free	According to IEC 60754-2
Resistance to oil	DIN VDE 0473, T. 811-2-1
Other resistance	Ozone and UV resistant

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

1171602

<https://www.phoenixcontact.com/us/products/1171602>

Classifications

ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

ETIM

ETIM 9.0	EC002607
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%