

SAC-4P-M 8MS/ 0,2-PVC/M 8FS - Sensor/actuator cable



1400506

<https://www.phoenixcontact.com/us/products/1400506>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PVC, black RAL 9005, Plug straight M8, coding: A, on Socket straight M8, cable length: 0.2 m

Commercial data

Item number	1400506
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1BCA
GTIN	4046356499002
Weight per piece (including packing)	14.58 g
Weight per piece (excluding packing)	14.58 g
Country of origin	DE

SAC-4P-M 8MS/ 0,2-PVC/M 8FS - Sensor/actuator cable



1400506

<https://www.phoenixcontact.com/us/products/1400506>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug straight M8
Number of positions	4
Coding type	A

Connection 2

Type	Socket straight M8
Number of positions	4

Cable/line

Cable length	0.2 m
--------------	-------


SAC-4P-M 8MS/ 0,2-PVC/M 8FS - Sensor/actuator cable



1400506

<https://www.phoenixcontact.com/us/products/1400506>

PVC black [PVC]

Dimensional drawing	
Cable weight	33 kg/km
UL AWM Style	2464 / 1729 (80°C/300 V)
Number of positions	4
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross section	4x 0.25 mm² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.05 mm
External cable diameter	4.40 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation) ≥ 0.76 mm (Outer cable sheath)
Overall twist	4 wires, twisted
Max. conductor resistance	max. 79 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Smallest bending radius, fixed installation	22 mm
Flame resistance	As per UL-Style 2464
Resistance to oil	EN 60811-2-1
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -10 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68

SAC-4P-M 8MS/ 0,2-PVC/M 8FS - Sensor/actuator cable



1400506

<https://www.phoenixcontact.com/us/products/1400506>

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


SAC-4P-M 8MS/ 0,2-PVC/M 8FS - Sensor/actuator cable

1400506

<https://www.phoenixcontact.com/us/products/1400506>


Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Dimensional drawing




Socket M8 x 1, straight

SAC-4P-M 8MS/ 0,2-PVC/M 8FS - Sensor/actuator cable

1400506


<https://www.phoenixcontact.com/us/products/1400506>

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

Schematic diagram




Pin assignment M8 socket, 4-pos., view female side

SAC-4P-M 8MS/ 0,2-PVC/M 8FS - Sensor/actuator cable

1400506

<https://www.phoenixcontact.com/us/products/1400506>

Circuit diagram



Contact assignment of M8 plugs/sockets

SAC-4P-M 8MS/ 0,2-PVC/M 8FS - Sensor/actuator cable



1400506

<https://www.phoenixcontact.com/us/products/1400506>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

UNSPSC

UNSPSC 21.0	31251501
-------------	----------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com