

# SAC-3P-M12MS/3,0-PUR/BI-1L-Z - Sensor/actuator cable



1400775

<https://www.phoenixcontact.com/us/products/1400775>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, on Valve connector BI (11 mm), Wiring: Z diode, cable length: 3 m

## Commercial data

Item number	1400775
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF07
Product key	AF1DMA
GTIN	4046356511520
Weight per piece (including packing)	122.4 g
Weight per piece (excluding packing)	114.9 g
Customs tariff number	85444290
Country of origin	PL

# SAC-3P-M12MS/3,0-PUR/BI-1L-Z - Sensor/actuator cable



1400775

<https://www.phoenixcontact.com/us/products/1400775>

## Technical data

### Product properties

Product type	Sensor/actuator cable with valve connector
Number of positions	3
No. of cable outlets	1

### Electrical properties

Nominal voltage $U_N$	24 V AC
	24 V DC

### Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	$\geq 100$

### Signaling

Status display	1 LED
Status display present	yes

### Connector

Connection 1	
Type	Plug straight M12
Coding type	A

Connection 2	
Type	Valve connector BI (11 mm)
Protective circuit	Z diode

### Cable/line

Cable length	3 m
--------------	-----

PUR halogen-free black [PUR]	
------------------------------	--

Dimensional drawing



Cable weight	30 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no

# SAC-3P-M12MS/3,0-PUR/BI-1L-Z - Sensor/actuator cable



1400775

<https://www.phoenixcontact.com/us/products/1400775>

Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	28x 0.15 mm
AWG signal line	20
Conductor cross section	3x 0.5 mm <sup>2</sup>
Wire diameter incl. insulation	1.5 mm ±0.05 mm (Signal line)
External cable diameter	4.50 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	39 Ω/km (at 20 °C)
Insulation resistance	min. 20 MΩ*km
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 1200 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	22.5 mm
Smallest bending radius, movable installation	45 mm
Dynamic load capacity (bending)	Max. bending cycles: 15000000, Bending radius: 50 mm, Traversing path: 0.9 m, Traversing rate: 5 m/s, Acceleration: 30 m/s <sup>2</sup>
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	according to DIN VDE 0482
	According to DIN EN 50265-2-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	largely oil-resistant
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -20 °C ... 80 °C (Cable, flexible installation)

# SAC-3P-M12MS/3,0-PUR/BI-1L-Z - Sensor/actuator cable



1400775

<https://www.phoenixcontact.com/us/products/1400775>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1400775>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387



**CSAus**

Approval ID: 13631

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	24 V	4 A	-	-

# SAC-3P-M12MS/3,0-PUR/BI-1L-Z - Sensor/actuator cable



1400775

<https://www.phoenixcontact.com/us/products/1400775>

## Classifications

### ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

### ETIM

ETIM 9.0	EC001855
----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

# SAC-3P-M12MS/3,0-PUR/BI-1L-Z - Sensor/actuator cable



1400775

<https://www.phoenixcontact.com/us/products/1400775>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	Lead monoxide (lead oxide)(CAS: 1317-36-8)
SCIP	3f8784f4-608c-4eb0-aea2-3f543f743c22

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)