

# SAC-4P-M12MS/ 5,0-186/M12FS - Sensor/actuator cable



1509568

<https://www.phoenixcontact.com/us/products/1509568>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PUR, black-gray RAL 7021, Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 5 m

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1509568       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF03          |
| Product key                          | AF1CCA        |
| GTIN                                 | 4017918899202 |
| Weight per piece (including packing) | 306 g         |
| Weight per piece (excluding packing) | 298.1 g       |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# SAC-4P-M12MS/ 5,0-186/M12FS - Sensor/actuator cable



1509568

<https://www.phoenixcontact.com/us/products/1509568>

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 4                     |
| No. of cable outlets | 1                     |
| Shielded             | no                    |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Seal material                          | NBR                                         |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 250 V AC                   |
|                       | 250 V DC                   |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |        |
|-------------------|--------|
| Tightening torque | 0.4 Nm |
|-------------------|--------|

### Connector

#### Connection 1

# SAC-4P-M12MS/ 5,0-186/M12FS - Sensor/actuator cable



1509568

<https://www.phoenixcontact.com/us/products/1509568>

|                     |                   |
|---------------------|-------------------|
| Type                | Plug straight M12 |
| Number of positions | 4                 |
| Coding type         | A                 |


## Connection 2

|                     |                     |
|---------------------|---------------------|
| Type                | Socket straight M12 |
| Number of positions | 4                   |
| Coding type         | A                   |

## Cable/line

|              |     |
|--------------|-----|
| Cable length | 5 m |
|--------------|-----|

## PUR POWER 0.75 mm² black [186]

|                                               |                                                                                     |
|-----------------------------------------------|-------------------------------------------------------------------------------------|
| Dimensional drawing                           |  |
| Cable weight                                  | 57 kg/km                                                                            |
| UL AWM Style                                  | 20549 / 1061 (80°C/300 V)                                                           |
| Number of positions                           | 4                                                                                   |
| Shielded                                      | no                                                                                  |
| Cable type                                    | PUR POWER 0.75 mm² black [186]                                                      |
| Conductor structure signal line               | 42x 0.15 mm                                                                         |
| AWG signal line                               | 18                                                                                  |
| Conductor cross section                       | 4x 0.75 mm² (power line)                                                            |
| Wire diameter incl. insulation                | 1.75 mm ±0.05 mm                                                                    |
| External cable diameter                       | 5.90 mm ±0.15 mm                                                                    |
| Outer sheath, material                        | PUR                                                                                 |
| External sheath, color                        | black-gray RAL 7021                                                                 |
| Conductor material                            | Bare Cu litz wires                                                                  |
| Material wire insulation                      | PVC                                                                                 |
| Single wire, color                            | brown, white, blue, black                                                           |
| Thickness, insulation                         | ≥ 0.23 mm (Core insulation)<br>≥ 0.76 mm (Outer cable sheath)                       |
| Overall twist                                 | 4 wires, twisted                                                                    |
| Max. conductor resistance                     | max. 26 Ω/km (at 20 °C)                                                             |
| Insulation resistance                         | ≥ 1 MΩ*km (at 20 °C)                                                                |
| Nominal voltage, cable                        | ≤ 300 V                                                                             |
| Test voltage                                  | ≥ 3000 V                                                                            |
| Minimum bending radius, fixed installation    | 5 x D                                                                               |
| Minimum bending radius, flexible installation | 10 x D                                                                              |

# SAC-4P-M12MS/ 5,0-186/M12FS - Sensor/actuator cable



1509568

<https://www.phoenixcontact.com/us/products/1509568>

|                                               |                                                                                                                         |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------|
| Smallest bending radius, fixed installation   | 30 mm                                                                                                                   |
| Smallest bending radius, movable installation | 59 mm                                                                                                                   |
| Dynamic load capacity (bending)               | Max. bending cycles: 2000000, Bending radius: 59 mm, Traversing path: 5 m, Traversing rate: 3 m/s, Acceleration: 5 m/s² |
| Flame resistance                              | according to UL 758/1581 (horizontal)                                                                                   |
|                                               | in accordance with UL 758/1581 FT2                                                                                      |
| Resistance to oil                             | According to DIN EN 60811-2-1, 168 h at 100°C                                                                           |
| Other resistance                              | hydrolysis and microbe resistant                                                                                        |
|                                               | Low adhesion                                                                                                            |
|                                               | abrasion-resistant                                                                                                      |
|                                               | Resistant to salt water                                                                                                 |
| Ambient temperature (operation)               | -25 °C ... 80 °C (cable, fixed installation)                                                                            |
|                                               | -5 °C ... 80 °C (Cable, flexible installation)                                                                          |

## Environmental and real-life conditions

### Ambient conditions

|                                                                   |                                                |
|-------------------------------------------------------------------|------------------------------------------------|
| Degree of protection                                              | IP65                                           |
|                                                                   | IP67                                           |
|                                                                   | IP68                                           |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket)               |
| Ambient temperature (operation) (Cable, fixed installation)       | -25 °C ... 80 °C (cable, fixed installation)   |
| Ambient temperature (operation) (Cable, flexible installation)    | -5 °C ... 80 °C (Cable, flexible installation) |


# SAC-4P-M12MS/ 5,0-186/M12FS - Sensor/actuator cable

1509568

<https://www.phoenixcontact.com/us/products/1509568>


## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, straight

# SAC-4P-M12MS/ 5,0-186/M12FS - Sensor/actuator cable

1509568

<https://www.phoenixcontact.com/us/products/1509568>

Schematic diagram




Pin assignment M12 plug, 4-pos., A-coded, view plug side

# SAC-4P-M12MS/ 5,0-186/M12FS - Sensor/actuator cable

1509568


<https://www.phoenixcontact.com/us/products/1509568>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Circuit diagram



Contact assignment of the M12 connector and the M12 socket

# SAC-4P-M12MS/ 5,0-186/M12FS - Sensor/actuator cable



1509568  
<https://www.phoenixcontact.com/us/products/1509568>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1509568>

|                                                                                                                                  |                       |                       |                   |                             |
|----------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>UL Listed</b><br>Approval ID: FILE E 221474 |                       |                       |                   |                             |
|                                                                                                                                  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                            |                       |                       |                   |                             |
|                                                                                                                                  | 300 V                 | 4 A                   | -                 | -                           |

|                                                                                                                                   |                       |                       |                   |                             |
|-----------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>cUL Listed</b><br>Approval ID: FILE E 221474 |                       |                       |                   |                             |
|                                                                                                                                   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                             |                       |                       |                   |                             |
|                                                                                                                                   | 300 V                 | 4 A                   | -                 | -                           |

|                                                                                                                                          |  |  |  |  |
|------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
|  <b>EAC-RoHS</b><br>Approval ID: RU D-DE.HB35.B.00387 |  |  |  |  |
|------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|



# SAC-4P-M12MS/ 5,0-186/M12FS - Sensor/actuator cable



1509568

<https://www.phoenixcontact.com/us/products/1509568>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-4P-M12MS/ 5,0-186/M12FS - Sensor/actuator cable



1509568

<https://www.phoenixcontact.com/us/products/1509568>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 2.568 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)