

## Contact Block LED 24V Module



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 453 0400
Specification	Contact Block LED 24V Module
HARTING eCatalogue	<a href="https://harting.com/09454530400">https://harting.com/09454530400</a>

### Identification

Category	Operator interfaces
Element	Contact block
Specification	LED (24 V)

### Version

Termination method	Screw termination
Number of contacts	2

### Technical characteristics

Conductor cross-section	0.5 ... 2.5 mm <sup>2</sup>
Rated current	≥0.001 A
Rated current	under laboratory conditions
Conditional short-circuit current	1,000 A
Stripping length	9 mm
Tightening torque	0.8 ... 1 Nm Screw terminal
Operating temperature	-25 ... +70 °C
Storage temperature	-50 ... +85 °C
Degree of protection acc. to IEC 60529	IP20
Lifetime	>40,000 h

### Material properties

Colour (insert)	White
RoHS	compliant



**Pushing Performance**  
Since 1945

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	EN 60947-5-1
----------------	--------------

## Commercial data

Packaging size	20
Net weight	14.5 g
Country of origin	Germany
European customs tariff number	85318070
GTIN	5713140450318
eCl@ss	27371209 Bulb socket block for command and alarm devices
ETIM	EC000204
UNSPSC 24.0	39111803