

MPP-CC-IDC-ix-10p-M-P-STR A-cod AWG28-26



Image is for illustration purposes only. Please refer to product description.

Part number	09 51 121 0001
Specification	MPP-CC-IDC-ix-10p-M-P-STR A-cod AWG28-26
HARTING eCatalogue	https://harting.com/09511210001

Identification

Category	Connectors
Series	HARTING Mini PushPull
Identification	HARTING ix Industrial®
Element	Connector sets
Features	Suitable for all PoE versions

Version

Termination method	IDC insulation displacement termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
further contacts	+ 2x GND
Coding	Type A
Locking type	PushPull
Pack contents	incl. housing, HARTING ix Industrial®-connector type A, shielding and cable gland

Technical characteristics

Conductor cross-section	0.09 ... 0.14 mm²
Conductor cross-section [AWG]	AWG 28 ... AWG 26
Wire outer diameter	≤1.2 mm
Rated current	1.5 A
Rated current	3 A per contact when used with 4 contacts (1,2,6,7)
Rated voltage	50 V AC 60 V DC



Pushing Performance
Since 1945

Technical characteristics

Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Insulation resistance	>100 MΩ
Contact resistance	≤30 mΩ
Shielding resistance	≤100 mΩ
Limiting temperature	-40 ... +70 °C
Storage temperature	-60 ... +85 °C
Relative humidity	95 % Non-condensing (operation)
	95 % Non-condensing (storage/transport)
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 / IP67
Cable diameter	5.5 ... 7.5 mm
Test voltage U _{r.m.s.}	0.5 kV (contact-contact)
	0.5 kV (contact-shielding)
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 2h/axis
	5.72 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	50 g / 11 ms, 3 shocks / axis and direction
	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (shielding)	Stainless steel
	Ni ≥ 1.6 µm Mating side (shielding)
	Sn ≥ 0.9 µm over Ni ≥ 0.9 µm Termination side (shielding)
Material (contacts)	Copper alloy
Surface (contacts)	PdNi ≥ 0.64 µm + Au ≥ 0.05 µm over Ni ≥ 2.6 µm Mating side
	Sn ≥ 3 µm over Ni ≥ 1.8 µm Termination side
Material (hood/housing)	Polybutylene terephthalate (PBT) / PA66
Colour (hood/housing)	Black
Material (seal)	HNBR / NBR
Colour (seal)	Black
Material (locking)	Polybutylene terephthalate (PBT)



Pushing Performance
Since 1945

Material properties

Colour (locking)	Yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
ECHA SCIP number	5b0b428a-c671-4c90-9b6d-16804ea5737a
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-3-124 Type A EN 50173-1
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	1
Net weight	9.86 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140223387
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408



Pushing Performance
Since 1945

Contact configuration



	10/100 Mbit/s	1/10 Gbit/s	TIA		PROFINET
			568 A	568 B	
1	TX+	BI_DA+	White/Green	White/Orange	Yellow
2	TX-	BI_DA-	Green	Orange	Orange
3	N.C	N.C	N.C	N.C	N.C
4	N.C	BI_DC+	Blue	Blue	N.C
5	N.C	BI_DC-	White/Blue	White/Blue	N.C
6	RX+	BI_DB+	White/Orange	White/Green	White
7	RX-	BI_DB-	Orange	Green	Blue
8	N.C	N.C	N.C	N.C	N.C
9	N.C	BI_DD+	White/Brown	White/Brown	N.C
10	N.C	BI_DD-	Brown	Brown	N.C