

## Acces. Special Cable Clamp EMC PG 13.5,



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 000 5004
Specification	Acces. Special Cable Clamp EMC PG 13.5,
HARTING eCatalogue	<a href="https://harting.com/09620005004">https://harting.com/09620005004</a>

### Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	EMC version

### Technical characteristics

Wrench size	22
Degree of protection acc. to IEC 60529	IP68
Size	Pg 13.5
Clamping range	9 ... 13 mm
Shielding diameter	6.5 ... 10.5 mm

### Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead 2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)
ECHA SCIP number	6fb545c1-f438-46c2-b07a-8552e7e5a3d7



Pushing Performance  
Since 1945

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	10
Net weight	34.4 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140072862
eCl@ss	27140803 Cable gland EMC (electrical installation)
ETIM	EC000441
UNSPSC 24.0	39121431