

RC-19P1N12F6NY - Coupler connector



1602602

<https://www.phoenixcontact.com/us/products/1602602>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 16+3, Direction of rotation: Standard, contact connection type: Pin, Solder cup, coding: N

Commercial data

Item number	1602602
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFG
GTIN	4046356240598
Weight per piece (including packing)	102.8 g
Weight per piece (excluding packing)	99.17 g
Country of origin	DE

RC-19P1N12F6NY - Coupler connector



1602602

<https://www.phoenixcontact.com/us/products/1602602>

Technical data

Product properties

Product type	Circular connector (cable-side)
Thread type	M23

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Insulating body

Coding	N
Material (Insulating body)	PA 6.6
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	19
Direction of rotation	Standard
Connection profile	16+3
Number Contact (Contact group 1)	3
Diameter Contact (Contact group 1)	1.5 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	10 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number Contact (Contact group 2)	16
Diameter Contact (Contact group 2)	1 mm
Litz wire cross-section min. Contact (Contact group 2)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A

Housing

Order information:	Order contact inserts and cable clamping/shield accessories separately
Type	Coupling housing
Thread type	M23
Design	straight

RC-19P1N12F6NY - Coupler connector



1602602

<https://www.phoenixcontact.com/us/products/1602602>

Type of locking	Screw locking mechanism
Pg screw connection	none
Housing material	Metal
Degree of protection (plugged in)	IP67

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------


RC-19P1N12F6NY - Coupler connector

1602602

<https://www.phoenixcontact.com/us/products/1602602>

Drawings

Schematic diagram




Connector pin assignment

RC-19P1N12F6NY - Coupler connector

1602602

<https://www.phoenixcontact.com/us/products/1602602>

Schematic diagram




Connector pin assignment

RC-19P1N12F6NY - Coupler connector

1602602

<https://www.phoenixcontact.com/us/products/1602602>

Schematic diagram



Dimensional drawing

RC-19P1N12F6NY - Coupler connector



1602602

<https://www.phoenixcontact.com/us/products/1602602>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-19P1N12F6NY - Coupler connector



1602602

<https://www.phoenixcontact.com/us/products/1602602>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	33c60306-bb5e-4274-b647-6b40c7180d00

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com