

RM-12S1N8A1100 - Cable connector



1613264

<https://www.phoenixcontact.com/us/products/1613264>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: RM, straight, shielded: no, Screw locking mechanism, No. of pos. : 12, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1613264
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFA
GTIN	4046356399036
Weight per piece (including packing)	73.9 g
Weight per piece (excluding packing)	69.47 g
Customs tariff number	85366990
Country of origin	DE

RM-12S1N8A1100 - Cable connector



1613264

<https://www.phoenixcontact.com/us/products/1613264>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number Contact (Contact group 1)	12
Diameter Contact (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	M16 x 1.5
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65 IP67 IP68

Environmental and real-life conditions

Ambient conditions

RM-12S1N8A1100 - Cable connector



1613264

<https://www.phoenixcontact.com/us/products/1613264>

Permissible humidity (storage/transport)
--

50 % ... 65 %


RM-12S1N8A1100 - Cable connector

1613264

<https://www.phoenixcontact.com/us/products/1613264>

Drawings

Schematic diagram



Connector pin assignment


RM-12S1N8A1100 - Cable connector

1613264

<https://www.phoenixcontact.com/us/products/1613264>



Schematic diagram



Connector pin assignment

RM-12S1N8A1100 - Cable connector



1613264

<https://www.phoenixcontact.com/us/products/1613264>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RM-12S1N8A1100 - Cable connector



1613264

<https://www.phoenixcontact.com/us/products/1613264>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	19d2db11-6e3c-43b5-9342-c862123178df

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com