

MIN D FE 9p STR S4 with 4-40 UNC spacer




Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 67 009 9072 |
| Specification | MIN D FE 9p STR S4 with 4-40 UNC spacer |
| HARTING eCatalogue | https://harting.com/09670099072 |

Identification

| | |
|----------------------------|--------------------|
| Category | Connectors |
| Series | D-Sub |
| Identification | Standard |
| Element | Connector |
| Description of the contact | Turned Straight |

Version

| | |
|--------------------|--|
| Termination method | Wave soldering termination |
| Gender | Female |
| Size | D-Sub 1 |
| Connection type | Motherboard to daughtercard Mezzanine |
| Number of contacts | 9 |
| Termination length | 3.7 mm |
| PCB fixing | With board locks |
| Locking type | Fixing flange with thread 4-40 UNC |

Technical characteristics

| | |
|-----------------------|---------------------|
| Distance between rows | 2.84 mm |
| Rated current | 7.5 A |
| Clearance distance | ≥1 mm |
| Creepage distance | ≥1 mm |
| Insulation resistance | >10 ¹⁰ Ω |



Pushing Performance
Since 1945

Technical characteristics

| | |
|---------------------------|-------------------------------|
| Contact resistance | ≤10 mΩ |
| Limiting temperature | -55 ... +125 °C |
| Performance level | NM 30 (S4) 1 |
| Mating cycles | ≥500 |
| Test voltage $U_{r.m.s.}$ | 1 kV |
| Isolation group | IIIa ($175 \leq CTI < 400$) |
| PCB thickness | ≥1.6 mm |
| Installation height | 7.4 mm |
| Hot plugging | No |

Material properties

| | |
|---|---|
| Material (insert) | Thermoplastic resin, glass-fibre filled (PBTP) Shell: Plated steel |
| Colour (insert) | White |
| Material (contacts) | Copper alloy |
| Surface (contacts) | Noble metal over Ni |
| Layer thickness | ≥0.76 μm |
| Layer thickness | ≥30 μinch |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| ECHA SCIP number | ecef7555-f643-4ceb-a337-fc54762297f1 |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |

Specifications and approvals

| | |
|----------------|-----------|
| Specifications | DIN 41652 |
|----------------|-----------|

| | |
|--------------------------------|------------------------|
| Packaging size | 50 |
| Net weight | 9.56 g |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| GTIN | 5713140089945 |
| eCl@ss | 27440214 D-Sub coupler |
| ETIM | EC001136 |
| UNSPSC 24.0 | 39121469 |