

## M12 T-cod 4-pol st/st m/f PUR 10m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 21 34 363 7446 100                                                                  |
| Specification      | M12 T-cod 4-pol st/st m/f PUR 10m                                                   |
| HARTING eCatalogue | <a href="https://harting.com/21343637446100">https://harting.com/21343637446100</a> |

### Identification

|               |                                 |
|---------------|---------------------------------|
| Category      | System cabling                  |
| Series        | Circular connectors M12         |
| Element       | Cable assemblies                |
| Specification | Pre-assembled on both sides     |
| Connector 1   | M12 T-coding<br>Male Straight   |
| Connector 2   | M12 T-coding<br>Female Straight |
| Type of cable | Copper cable (round)            |

### Version

|                 |                        |
|-----------------|------------------------|
| Cable length    | 10 m                   |
| Number of cores | 4                      |
| Core structure  | 4x 1.5 mm <sup>2</sup> |
| Coding          | T-coding               |

### Technical characteristics

|                      |                |
|----------------------|----------------|
| Rated current        | 12 A           |
| Rated voltage        | 63 V DC        |
| Limiting temperature | -25 ... +80 °C |
| Cable diameter       | 7.2 mm         |

### Material properties

|                  |                    |
|------------------|--------------------|
| Material (cable) | PUR (polyurethane) |
|------------------|--------------------|



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| Colour (cable)                       | Black                                                  |
| RoHS                                 | compliant with exemption                               |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50                                                     |
| REACH Annex XVII substances          | Not contained                                          |
| REACH ANNEX XIV substances           | Not contained                                          |
| REACH SVHC substances                | Yes                                                    |
| REACH SVHC substances                | Lead                                                   |
| ECHA SCIP number                     | 567c8b78-5fa0-43aa-a4c0-beb9d99b7769                   |
| California Proposition 65 substances | Yes                                                    |
| California Proposition 65 substances | Lead<br>Nickel                                         |

## Specifications and approvals

|           |    |
|-----------|----|
| Approvals | CE |
|-----------|----|

## Commercial data

|                                |                                         |
|--------------------------------|-----------------------------------------|
| Packaging size                 | 1                                       |
| Net weight                     | 960 g                                   |
| Country of origin              | Germany                                 |
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140815889                           |
| eCl@ss                         | 27060311 Assembled sensor actuator-line |
| ETIM                           | EC002599                                |
| UNSPSC 24.0                    | 26121604                                |