

## M12 A-cod 4-pol an/- f/- PVC 10m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 21 35 040 0416 100                                                                  |
| Specification      | M12 A-cod 4-pol an/- f/- PVC 10m                                                    |
| HARTING eCatalogue | <a href="https://harting.com/21350400416100">https://harting.com/21350400416100</a> |

### Identification

|               |                               |
|---------------|-------------------------------|
| Category      | System cabling                |
| Series        | Circular connectors M12       |
| Element       | Cable assemblies              |
| Specification | Pre-assembled on one side     |
| Connector 1   | M12 A-coding<br>Female Angled |
| Type of cable | Copper cable (round)          |

### Version

|                 |                         |
|-----------------|-------------------------|
| Cable length    | 10 m                    |
| Number of cores | 4                       |
| Core structure  | 4x 0.34 mm <sup>2</sup> |
| Coding          | A-coding                |

### Material properties

|                  |        |
|------------------|--------|
| Material (cable) | PVC    |
| Colour (cable)   | Yellow |

### Commercial data

|                   |               |
|-------------------|---------------|
| Packaging size    | 1             |
| Net weight        | 370.5 g       |
| Country of origin | Mexico        |
| GTIN              | 5713140810334 |



Pushing Performance  
Since 1945

Commercial data

|             |                                         |
|-------------|-----------------------------------------|
| eCl@ss      | 27060311 Assembled sensor actuator-line |
| UNSPSC 24.0 | 26121604                                |