

M23_19P FE,Int-thread,ANG PUR cable,10M



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 21 37 360 0D74 100 |
| Specification | M23_19P FE,Int-thread,ANG PUR cable,10M |
| HARTING eCatalogue | https://harting.com/21373600D74100 |

Identification

| | |
|----------------|--|
| Category | System cabling |
| Series | Circular connectors M23 |
| Identification | Signal |
| Element | Cable assemblies |
| Specification | Pre-assembled on one side |
| Connector 1 | M23 Female Angled |
| Type of cable | Copper cable (round) |
| Features | Flame retardancy Oil and UV resistant Highly EMC resistant Halogen freeness |

Version

| | |
|-----------------|------------------------|
| Cable length | 10 m |
| Number of cores | 19 |
| Core structure | 3x AWG 18 + 16x AWG 22 |

Technical characteristics

| | |
|------------------------|----------------|
| Rated voltage | 150 V |
| Rated current (signal) | 2 A |
| Rated current (power) | 9 A |
| Limiting temperature | -40 ... +80 °C |



Pushing Performance
 Since 1945

Technical characteristics

| | |
|--|------|
| Degree of protection acc. to IEC 60529 | IP67 |
|--|------|

Material properties

| | |
|--------------------------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Silver plated |
| Material (cable) | PUR (polyurethane) |
| Colour (cable) | Black |
| Material (overmoulding) | Thermoplastic polyurethane (TPU) |
| Colour (overmoulding) | Black |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| ECHA SCIP number | 567c8b78-5fa0-43aa-a4c0-beb9d99b7769 |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 1 |
| Net weight | 1,400 g |
| Country of origin | China |
| European customs tariff number | 85444290 |
| GTIN | 5713140241312 |
| eCl@ss | 27060311 Assembled sensor actuator-line |
| ETIM | EC001855 |
| UNSPSC 24.0 | 26121604 |