



Pushing Performance
Since 1945

Ha-VIS eCon 2050GX-I-AWT



Image is for illustration purposes only. Please refer to product description.

Part number	24 14 405 0002
Specification	Ha-VIS eCon 2050GX-I-AWT
HARTING eCatalogue	https://harting.com/24144050002

Identification

Series	Ha-VIS eCon 2000
Identification	Advanced
Element	Industrial Ethernet Switches
Specification	Unmanaged
Type of Ethernet	Full Gigabit Ethernet

Version

Total number of ports	5
Fixing	Wall mounting flat
Switching technology	Store and Forward
Frame size	10 kB
MAC table size	8k Entries
MAC-address filter	LLDP and PROFINET PTCP Delay (01-80-C0-00-00-0E) blocked
Packet buffer size	4 Megabit
Non blocking	Yes
Quality of service	Yes
Flow control	Off
Signal contact	No
PoE functionality	No
Jumbo frame support	Yes
Conformal coating of PCB	Yes
Field of application	Indoor usage



Pushing Performance
Since 1945

Version

Pack contents	Pluggable and screwable Push-In contact for power supply Assembly instructions
---------------	---

Termination data

Nominal voltage	24 V DC 48 V DC
Permissible voltage	9 ... 60 V DC
Surge protection	Yes
Operating current	130 mA @ 24 V DC 70 mA @ 48 V DC
Supply circuit	SELV (Circuit Breaker 10 A)
Starting current	1.2 A @ 24 V DC 2.7 A @ 48 V DC
Overcurrent protection	4 A at input
Power consumption	3.1 W @ 24 V DC 3.4 W @ 48 V DC
Termination method	Pluggable and screwable Push-In contact for power supply
Number of contacts	3
Conductor cross-section	0.14 ... 1.5 mm ²
Conductor cross-section [AWG]	AWG 30 ... AWG 14
Pinout	+ / - / FE
Reverse polarity protection	Yes

Technical characteristics

Operating temperature	-40 ... +70 °C
Storage temperature	-40 ... +85 °C
Relative humidity	0 ... 95 % Non-condensing (operation) 0 ... 95 % Non-condensing (storage/transport)
Air pressure	≥795 hPa ≈ 2000 m
Degree of protection acc. to IEC 60529	IP30 mated condition

Ethernet ports copper

10/100/1000 Mbit/s (ix Industrial [®] -Ports)	5
Transmission standard	10BASE-T 100BASE-TX 1000BASE-T
Auto-negotiation	Yes



Pushing Performance
Since 1945

Ethernet ports copper

Auto-polarity	Yes
Auto-MDI(X)	Yes
Transmission physics	Twisted Pair Cat. 5
Data rate	10 Mbit/s
	100 Mbit/s
	1,000 Mbit/s
Transmission length	100 m

Material properties

Material (hood/housing)	Aluminium (anodised)
Length	24 mm
Width	80.4 mm
Height	113 mm

Specifications and approvals

Specifications	EN 61000-6-1 EMC Interference immunity
	EN 61000-6-2 EMC Interference immunity
	EN 55024 EMC Interference immunity
	EN 61000-4-2 Electrostatic discharge (ESD)
	EN 61000-4-3 Electromagnetic field
	EN 61000-4-4 Rapid transients (burst)
	EN 61000-4-6 conducted disturbances
	EN 61000-6-4 emission standard
	EN 55032 emission standard
	FCC 47 FCR Part 15
	IEC 60721-3-3 Mechanical stability (class 3M4)
	IEC 60068-2-6 Vibration (sinusoidal)
	IEC 60068-2-27 Shock
	IEEE 802.3
	IEC 61076-3-124 Type A
UL / CSA	UL in preparation
Approvals	CE
	DNV GL in preparation
	E1 in preparation
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	169 g
Country of origin	Germany



Pushing Performance
Since 1945

Commercial data

European customs tariff number	85176200
GTIN	5713140194960
eCl@ss	19170130 Network switch (general application)
ETIM	EC000734
UNSPSC 24.0	43222612