




FRONT VIEW



LEFT VIEW
CONNECTOR COLOR: WHITE



RIGHT VIEW
CONNECTOR COLOR: GREY



PIN	FUNCTION	COLOR	CONNECT TO
1	BATTERY +	RED	UPS BAT +
2	BATTERY N	WHITE	UPS BAT N
3	BATTERY -	BLACK	UPS BAT -

SPECIFICATION

1. STANDARD:
- CABLE TYPE:UL2587 90°C 600V
- CABLE DIAMETER:3-CORE Ø21.8/1-CORE Ø8.5
- 6AWG, 3 CONDUCTORS
- USE WITH UPS CAPACITY: 10/15/20kVA
- WORKMANSHIP STANDARD: HARNESS TO BE MANUFACTURED TO IPC/WHMA-A-620 CLASS 2 STANDARD
2. ADDITIONAL:
- NONE
3. ACCESSORIES:
- BATTERY TEMPERATURE DETECTION 5 METER CABLE (1PC)

- NOTES:
1. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
2. 100% TESTING TO BE CARRIED OUT PRIOR TO SHIPPING: MUST BE TESTED FOR CONTINUITY, OPENS, SHORTS & WIRE MAPPING

IDENTIFICATION /PN TABLE:		
PART NUMBER	DESCRIPTION	SHIPPING WEIGHT (KG)
UVP10T20VCBL	EBP POWER CABLE 480VDC & BATTERY TEMPERATURE DETECTION CABLE 5 METER, FOR 10, 15, 20kVA VRLA THREE PHASE UPS	4.7

					FILE		BATTERY CABLE UVP10T20VCBL CUSTOMER DRAWING				
					NEW NUMBER UVP10T20VCBL REVISED FROM UVP10T20VCBL						
					ALL TOLERANCES ARE +/-100mm UNLESS OTHERWISE SPECIFIED				N/A		
QDA	06/13/2024	HQ	JOSD	RRG/ALD	RELEASE TO PRODUCTION			005385			
REV	DATE	BY	CHK	APR	DESCRIPTION			ECN	DATE	FILE	
								06/13/2024	VARIOUS		
								SHT 1 OF 1	B		