


Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Markers for marking terminal blocks from Weidmüller, Conta Clip, and Klemсан, 20-section, unmarked, can be marked with THERMOMARK CARD and BLUEMARK, color: blue



Commercial data

Item number	0833053
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BG211C
Catalog page	Page 169 (C-3-2019)
GTIN	4046356984959
Weight per piece (including packing)	2.134 g
Weight per piece (excluding packing)	2.134 g
Country of origin	PL

UM1-TM (6X12) BU - Marker for terminal blocks



0833053

<https://www.phoenixcontact.com/us/products/0833053>

Technical data

Product properties

Product type	Terminal marking
Pitch	6 mm
Type	high

Marking

Number of individual labels	20
Number of individual labels per row	10
Number of marker strips	2

Dimensions

Width	6 mm
Length	12 mm
Pitch	6 mm

Material specifications

RoHS compliant	yes
Color	blue (RAL 5015)
Material	PC
Flammability rating according to UL 94	V2
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed

UM1-TM (6X12) BU - Marker for terminal blocks



0833053

<https://www.phoenixcontact.com/us/products/0833053>

Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	snap in
---------------	---------

UM1-TM (6X12) BU - Marker for terminal blocks



0833053

<https://www.phoenixcontact.com/us/products/0833053>

Classifications

ETIM

ETIM 8.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UM1-TM (6X12) BU - Marker for terminal blocks



0833053
<https://www.phoenixcontact.com/us/products/0833053>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com