

1340151  
<https://www.phoenixcontact.com/us/products/1340151>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coaxial PCB connector, degree of protection: IP20, number of positions: 1, 12 Gbps, material: Metal, connection method: Solder connection, cable outlet: straight, for additional information, see the product range drawing in the Download Center

Your advantages

- Complete documentation saves developers time during design-in
- Ideal for WLAN, Bluetooth, LTE, and 5G signals
- The reflow capability of PCB connectors enables efficient and cost-optimized processing

Commercial data

Item number	1340151
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB14
Product key	ABNFBA
GTIN	4063151646608
Weight per piece (including packing)	6.85 g
Weight per piece (excluding packing)	3.82 g
Customs tariff number	85366910
Country of origin	DE

# CUC-COX-J1M-A/KFS - Coaxial PCB connector



1340151

<https://www.phoenixcontact.com/us/products/1340151>

## Technical data

### Product properties

Product type	Data connector (device side)
Type	Coaxial
Number of positions	1
Connection profile	R-SMA (f)
Type of packaging	Tape and Reel
Type	Socket
Cable outlet	straight
Thread type	1/4-36 UNS

### Electrical properties

Rated surge voltage (III/2)	1500 V
Frequency range	10 Hz
Test voltage	1000 V <sub>rms</sub>
Transmission medium	Copper

### Output data

Transmission frequency	1.00 GHz
------------------------	----------

### Connection data

#### Connection technology

Connection method	Solder connection
Locking mechanism tightening torque	1.10 Nm

### Dimensions

Width	6.5 mm
Height	11.6 mm
Length	14.2 mm
Installed height	9.60 mm
Orientation to PCB	90.00 °

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Contact material	CuBe2
Contact surface material	NiP-Au

### Cable/line

Halogen-free	no
--------------	----

### Mechanical properties

# CUC-COX-J1M-A/KFS - Coaxial PCB connector



1340151

<https://www.phoenixcontact.com/us/products/1340151>

## Mechanical data

Insertion/withdrawal cycles	> 100
Extraction force per signal contact	< 20 N
Locking mechanism tightening torque	1.10 Nm

## Environmental and real-life conditions

### Test specification

Specification	DIN EN 61169-1
Contact resistance $R_2$	2.00 mΩ
Insulation resistance, neighboring contacts	5 GΩ
Impulse withstand voltage at sea level	1400.00 V DC
Power-frequency withstand voltage	1000.00 V AC

### Test specification

Specification	DIN EN 60068-2-14 Test Na
Cold stress	-10°C

### Test specification

Specification	DIN EN 60068-2-6 Test Fc
Frequency	10-2000-10 Hz
Sweep speed	1 octave/min
Amplitude	0.75 mm
Acceleration	100.00 m/s <sup>2</sup>
Test duration	2.50 h

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 125 °C
Ambient temperature (storage/transport)	-55 °C ... 125 °C


## Mounting

### Processing notes

Process	THR
Moisture Sensitive Level	MSL 1

## Drawings

Diagram



Classification reflow soldering profile

# CUC-COX-J1M-A/KFS - Coaxial PCB connector



1340151

<https://www.phoenixcontact.com/us/products/1340151>

## Classifications

### ECLASS

ECLASS-13.0	27460201
-------------	----------

### ETIM

ETIM 9.0	EC002637
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CUC-COX-J1M-A/KFS - Coaxial PCB connector



1340151

<https://www.phoenixcontact.com/us/products/1340151>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)