

WST 2,5 - Warning cover

3030941

<https://www.phoenixcontact.com/us/products/3030941>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Warning cover, 5-pos., for terminal width: 5.2 mm

Your advantages

- Accidental actuation of the terminal points is prevented
- Warning labels and warning covers serve to cover and identify mains terminal blocks
- The warning labels snap into the screw and actuation shafts of the relevant terminal block
- Can be isolated lengthwise and crosswise

Commercial data

Item number	3030941
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG20
Product key	BG2511
GTIN	4017918193102
Weight per piece (including packing)	0.32 g
Weight per piece (excluding packing)	0.314 g
Customs tariff number	49119900
Country of origin	PL

WST 2,5 - Warning cover

3030941

<https://www.phoenixcontact.com/us/products/3030941>



Technical data

Product properties

Product type	Klemmenmarker
Number of positions	5
Pitch	4.25 mm

Marking

Number of individual labels	5
Number of individual labels per row	5
Identification technology	Plotter

Dimensions

Width	4.55 mm
Height	4.25 mm
Depth	4.50 mm
Pitch	4.25 mm

Material specifications

Color	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
---------------	-------------------------------------

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

WST 2,5 - Warning cover

3030941

<https://www.phoenixcontact.com/us/products/3030941>



Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	plug in
---------------	---------

WST 2,5 - Warning cover

3030941

<https://www.phoenixcontact.com/us/products/3030941>



Classifications

ECLASS

ECLASS-13.0	27281107
ECLASS-15.0	27281107

ETIM

ETIM 9.0	EC001777
----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

WST 2,5 - Warning cover



3030941
<https://www.phoenixcontact.com/us/products/3030941>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.003 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com