

SAC-4P-MRDC1/2,5-936 SCO - Sensor/actuator cable



1443048

<https://www.phoenixcontact.com/us/products/1443048>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PE-X halogen-free, black RAL 9005, Plug angled M12 SPEEDCON, coding: D, on free cable end, cable length: 2.5 m

Commercial data

Item number	1443048
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CJN
GTIN	4046356538022
Weight per piece (including packing)	231.5 g
Weight per piece (excluding packing)	232.3 g
Country of origin	DE

SAC-4P-MRDC1/2,5-936 SCO - Sensor/actuator cable



1443048

<https://www.phoenixcontact.com/us/products/1443048>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	4

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

Connector

Connection 1

Type	Plug angled M12 SPEEDCON
Number of positions	4
Locking type	SPEEDCON
Coding type	D (Data)

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	2.5 m
--------------	-------

PROFINET RADOX® railway application CAT5 reinforced [936]

Dimensional drawing	
Cable weight	81 g/m
Number of positions	4
Shielded	yes
Cable type	PROFINET RADOX® railway application CAT5 reinforced [936]
Conductor structure	1x4xAWG22/7, SF/TQ
Signal speed	66 c
Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Conductor cross section	4x 0.34 mm ²
Wire diameter incl. insulation	1.95 mm
External cable diameter	7.25 mm ±0.3 mm
Outer sheath, material	PE-X

SAC-4P-MRDC1/2,5-936 SCO - Sensor/actuator cable



1443048

<https://www.phoenixcontact.com/us/products/1443048>

External sheath, color	black RAL 9005
Conductor material	silver-plated Cu litz wires
Material wire insulation	PE-X
Single wire, color	white-blue, orange-yellow
Thickness, outer sheath	≥ 0.80 mm
Overall twist	Star quad
Optical shield covering	100 %
Max. conductor resistance	≤ 54.4 Ω/km
Coupling resistance	200.00 mΩ/m (f ≤ 30 MHz)
Wave impedance	100 Ω ±5 Ω (f = 100 MHz)
Working capacitance	≤ 65 pF (Line-line)
	≤ 100 pF (Line-shield)
Nominal voltage, cable	300 V AC
Test voltage	2000 V AC (50 Hz, 5 minutes)
Minimum bending radius, fixed installation	6 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	44 mm
Smallest bending radius, movable installation	73 mm
Near end crosstalk attenuation (NEXT)	80 dB (with 1 MHz)
	76 dB (at 4 MHz)
	67 dB (at 10 MHz)
	60 dB (at 31.5 MHz)
	56 dB (at 62.5 MHz)
	53 dB (at 100 MHz)
Return attenuation (RL)	35 dB (at 4 MHz)
	35 dB (at 10 MHz)
	35 dB (at 31.5 MHz)
	33 dB (at 62.5 MHz)
	33 dB (at 100 MHz)
Remote crosstalk attenuation (FEXT)	80 dB (with 1 MHz)
	70 dB (at 4 MHz)
	65 dB (at 10 MHz)
	58 dB (at 31.5 MHz)
	59 dB (at 62.5 MHz)
	67 dB (at 100 MHz)
Shield attenuation	2 dB (with 1 MHz)
	4 dB (at 4 MHz)
	6.5 dB (at 10 MHz)
	10.5 dB (at 31.5 MHz)
	14 dB (at 62.5 MHz)
	18 dB (at 100 MHz)
	40.00 dB (30 MHz ≤ f ≤ 100 MHz)
Halogen-free	in accordance with EN 50267-2-1
	IEC 60332-1-2

SAC-4P-MRDC1/2,5-936 SCO - Sensor/actuator cable



1443048

<https://www.phoenixcontact.com/us/products/1443048>

Flame resistance	EN 50266
	EN 60332-3-25
	NF C32-070, 2.1
	NF C32-070, 2.2
	UL 1685, 12 (FT4)
	in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)
Fume corrosiveness	EN 50267-2-2
Fume toxicity	BS 6853 B.1
	EN 50305, 9.2
Concentration of fumes	BS 6853 D.8.7
	EN 61034-2
	UL 1685, 12 (FT4)
Resistance to oil	according to IRM 902, 72 h at 100 °C
Fire protection in rail vehicles	BS 6853 (Category Ia, Ib, II)
	GM/RT 2130 (Category Ia, Ib, II)
	EN 45545 (Risk level HL1 - HL3)
	DIN 5510 (Fire protection level 1, 2, 3, 4)
	NF F16-101 (Category A1, A2, B)
	NF F16-101 (Class C/F0)
	NFPA 130
	UNI CEI 11170 (Risk level LR1 - LR4)
Other resistance	Resistance to fuels (according to IRM 903, 168 h at 70 °C)
Ambient temperature (operation)	-50 °C ... 90 °C (cable, fixed installation)
	-40 °C ... 90 °C (Cable, flexible installation)

SAC-4P-MRDC1/2,5-936 SCO - Sensor/actuator cable



1443048

<https://www.phoenixcontact.com/us/products/1443048>

Classifications

ECLASS

ECLASS-13.0	27060307
-------------	----------

UNSPSC

UNSPSC 21.0	31251501
-------------	----------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com