

# SACC-CI-M12FS-8CON-L180-THR SH - Contact carrier



1551422

<https://www.phoenixcontact.com/us/products/1551422>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 8-position, Socket, straight, M12, coding: A, PCB mounting, THR solder connection, this item is undergoing a smooth changeover, lead-free alternative in accordance with RoHS II without exception 6c (Pb < 0.1%) possible on request in advance

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

## Commercial data

Item number	1551422
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB23
Product key	ABQAGG
Catalog page	Page 257 (C-2-2013)
GTIN	4046356153706
Weight per piece (including packing)	5.29 g
Weight per piece (excluding packing)	2.695 g
Customs tariff number	85366990
Country of origin	DE

# SACC-CI-M12FS-8CON-L180-THR SH - Contact carrier



1551422

<https://www.phoenixcontact.com/us/products/1551422>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Application	Signal
Number of positions	8
Seal present	yes
Shielded	yes
Coding	A
Thread type	M12

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V
Nominal current $I_N$	2 A

### Connection data

Connection method	THR solder connection
-------------------	-----------------------

### Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM / EPDM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PPA

### Connector

#### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12

# SACC-CI-M12FS-8CON-L180-THR SH - Contact carrier



1551422

<https://www.phoenixcontact.com/us/products/1551422>

Coding	A
--------	---

## Cable/line

Ambient temperature (operation)	-40 °C ... 85 °C (cable, fixed installation)
	-25 °C ... 85 °C (Cable, flexible installation)

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)
	-25 °C ... 85 °C (Cable, flexible installation)
	-40 °C ... 85 °C (cable, fixed installation)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

## Mounting

Mounting type	PCB mounting
---------------	--------------

## Packaging specifications

Type of packaging	Tray
-------------------	------

# SACC-CI-M12FS-8CON-L180-THR SH - Contact carrier




1551422

<https://www.phoenixcontact.com/us/products/1551422>

## Drawings

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side


# SACC-CI-M12FS-8CON-L180-THR SH - Contact carrier



1551422  
<https://www.phoenixcontact.com/us/products/1551422>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1551422>

	<b>UL Recognized</b> Approval ID: E118976-20100522			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	30 V	2 A	24	-

# SACC-CI-M12FS-8CON-L180-THR SH - Contact carrier



1551422  
<https://www.phoenixcontact.com/us/products/1551422>

## Classifications

### ECLASS

ECLASS-13.0	27440110
-------------	----------

### ETIM

ETIM 9.0	EC003568
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CI-M12FS-8CON-L180-THR SH - Contact carrier



1551422

<https://www.phoenixcontact.com/us/products/1551422>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2e95e33a-6b13-4adf-9d57-19cf0aa6bd48

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)