

# UDB 2X35/25 BK - Trunk line branch terminal



3071351

<https://www.phoenixcontact.com/us/products/3071351>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Trunk line branch terminal, nom. voltage: 400 V, nominal current: 125 A, number of connections: 4, number of positions: 1, connection method: Screw connection, Rated cross section: 35 mm<sup>2</sup>, 1 level, cross section: 10 mm<sup>2</sup> - 35 mm<sup>2</sup>, Screw connection, 2nd level, cross section: 1.5 mm<sup>2</sup> - 25 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: black

## Your advantages

- The branch terminal is suitable for the simple voltage pick-off of main supply cables
- Conformance with DIN VDE 0603-2/EN 60998-1

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3071351       |
| Packing unit                         | 5 pc          |
| Minimum order quantity               | 5 pc          |
| Sales key                            | BE12          |
| Product key                          | BE1213        |
| GTIN                                 | 4046356735865 |
| Weight per piece (including packing) | 79.98 g       |
| Weight per piece (excluding packing) | 79.98 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

# UDB 2X35/25 BK - Trunk line branch terminal



3071351

<https://www.phoenixcontact.com/us/products/3071351>

## Technical data

### Notes

|         |                                   |
|---------|-----------------------------------|
| General | Up to 3 terminal blocks alignable |
|---------|-----------------------------------|

### Product properties

|                       |                             |
|-----------------------|-----------------------------|
| Product type          | Feed-through terminal block |
| Product family        | UDB                         |
| Number of positions   | 1                           |
| Number of connections | 4                           |
| Number of rows        | 1                           |
| Potentials            | 1                           |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 4.06 W |

### Connection data

|                                 |                    |
|---------------------------------|--------------------|
| Number of connections per level | 4                  |
| Nominal cross section           | 35 mm <sup>2</sup> |

#### 1 level

|                                                                   |                                           |
|-------------------------------------------------------------------|-------------------------------------------|
| Connection method                                                 | Screw connection                          |
| Screw thread                                                      | M6/M8                                     |
| Tightening torque                                                 | ... 4 Nm                                  |
| Stripping length                                                  | 25 mm                                     |
| Connection in acc. with standard                                  | IEC 60998-1                               |
| Conductor cross-section rigid                                     | 10 mm <sup>2</sup> ... 35 mm <sup>2</sup> |
| Cross section AWG                                                 | 6 ... 2 (converted acc. to IEC)           |
| Conductor cross-section flexible                                  | 10 mm <sup>2</sup> ... 25 mm <sup>2</sup> |
| Conductor cross-section, flexible [AWG]                           | 6 ... 4 (converted acc. to IEC)           |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 10 mm <sup>2</sup> ... 25 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 10 mm <sup>2</sup> ... 16 mm <sup>2</sup> |
| Nominal current                                                   | 125 A                                     |
| Maximum load current                                              | 125 A                                     |
| Nominal voltage                                                   | 400 V (max. 1000 V)                       |
| Note                                                              | Use ferrules for stranded conductors      |
| Nominal cross section                                             | 35 mm <sup>2</sup>                        |

#### 2nd level

|                   |                  |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

# UDB 2X35/25 BK - Trunk line branch terminal



3071351

<https://www.phoenixcontact.com/us/products/3071351>

|                                                                   |                    |
|-------------------------------------------------------------------|--------------------|
| Stripping length                                                  | 25 mm              |
| Connection in acc. with standard                                  | IEC 60998-1        |
| Conductor cross-section rigid                                     | 1.5 mm² ... 25 mm² |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 1.5 mm² ... 16 mm² |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 1.5 mm² ... 10 mm² |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 27 mm   |
| Height             | 55 mm   |
| Depth on NS 35/7,5 | 46 mm   |
| Depth on NS 35/15  | 53.5 mm |

## Material specifications

|                                        |                  |
|----------------------------------------|------------------|
| Color                                  | black (RAL 9005) |
| Flammability rating according to UL 94 | V0               |
| Insulating material group              | I                |
| Insulating material                    | PA               |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Environmental and real-life conditions

### Ambient conditions

|                                          |                                                                                                                              |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                                                    |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                                                                              |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                                                                              |
| Permissible humidity (operation)         | 20 % ... 90 %                                                                                                                |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                                                                                |

## Standards and regulations

|                                  |             |
|----------------------------------|-------------|
| Connection in acc. with standard | IEC 60998-1 |
|                                  | IEC 60998-1 |

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# UDB 2X35/25 BK - Trunk line branch terminal



3071351

<https://www.phoenixcontact.com/us/products/3071351>

## Drawings

Circuit diagram



# UDB 2X35/25 BK - Trunk line branch terminal



3071351

<https://www.phoenixcontact.com/us/products/3071351>

## Approvals

💡 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3071351>



**EAC**

Approval ID: KZ7500651131219505



**VDE Zeichengenehmigung**

Approval ID: 40055082

# UDB 2X35/25 BK - Trunk line branch terminal



3071351

<https://www.phoenixcontact.com/us/products/3071351>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250119 |
| ECLASS-15.0 | 27250119 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UDB 2X35/25 BK - Trunk line branch terminal



3071351  
<https://www.phoenixcontact.com/us/products/3071351>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |
| EF3.0 Climate Change                    |                                          |
| CO2e kg                                 | 0.423 kg CO2e                            |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)